

Product data sheet

Specifications



250V 20A Taiwan T-Shape 3 Pin Socket 2M Sized Module, Bronze

84426MTE_BZ

⚠ Discontinued on: Jun 30, 2023

⚠ Discontinued

Main

Product Or Component Type	Power socket-outlet
Outlet Poles Configuration	2P + E Taiwan
Load Type	Inductive
Cover Plate Colour Tint	Bronze

Complementary

Device Mounting	Flush Surface
Rated Current	20 A at 250 V AC 60 Hz
Number Of Gangs	1 gang
Material	Polycarbonate base Polycarbonate cover
Connections - Terminals	Screw terminals
Width	45.8 mm
Height	46.7 mm
Depth	39 mm

Environment

Ambient Air Temperature For Storage	-5...60 °C
Ambient Air Temperature For Operation	-5...40 °C
Relative Humidity	10...95 %, non-condensing (operating) 10...95 %, non-condensing (storage)
Environmental Characteristic	UV resistant indoor use
Operating Altitude	2000 m
Standards	CNS 690 BS 7671
Ip Degree Of Protection	IP20
Standards	BS 7671 CNS 690

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Height	4.7 cm
Package 1 Width	4.6 cm
Package 1 Length	3.9 cm
Package 1 Weight	47.0 g

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations