

# Product data sheet

Specifications



## selector switch Ø 30 - 2 positions - maintained - LED

9001K12J35LGG

 **Discontinued on:** Oct 11, 2019

 **Discontinued**

### Main

Range Of Product	Harmony 9001K
Product Or Component Type	Illuminated selector switch
Device Short Name	9001K
Type Of Operator	maintained
Operator Profile	Green standard knob

### Complementary

Bezel Material	Chromium plated metal
Mounting Diameter	30 mm
Net Weight	0.245 kg
Shape Of Signaling Unit Head	Round
Operator Position Information	2 positions
Contacts Type And Composition	Without contact block
Mechanical Durability	500000 cycles
Light Block Supply	Direct
Light Source	LED
Bulb Base	BA 9s
Light Block Colour	Green
[Us] Rated Supply Voltage	24...28 V AC/DC
Device Presentation	Basic element

### Environment

Protective Treatment	TC
Ambient Air Temperature For Storage	-40...70 °C
Ambient Air Temperature For Operation	-25...70 °C
Electrical Shock Protection Class	Class II conforming to IEC 61140
Ip Degree Of Protection	IP66 conforming to IEC 60529

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Nema Degree Of Protection	NEMA 1
	NEMA 12
	NEMA 13
	NEMA 2
	NEMA 3
	NEMA 3R
	NEMA 4
	NEMA 6
Standards	JIS C 852
	EN/IEC 60947-5-4
	CSA C22.2 No 14
	EN/IEC 60947-5-1
	UL 508
	EN/IEC 60947-1
Product Certifications	JIS C 4520
	NEMA
	UL 508
Vibration Resistance	7 gn (f= 2...500 Hz) conforming to IEC 60068-2-6
Shock Resistance	50 gn conforming to IEC 60068-2-27