



Main

Range of product	9007
Series name	Heavy duty
Product or component type	Snap limit switch
Device short name	9007AO/CO
Body type	Fixed

Complementary

Mounting mode	-
Operator profile	Plunger head
Material	Metal
Body material	Cast zinc
Operator material	Cast zinc
Fixing mode	By the body
Movement of operating head	Linear
Type of operator	Metal spring return roller lever plunger RH bracket + 0.47" roller
Switch actuation	By 30° cam
Type of approach	2 directions traverse approach
Electrical connection	1...2 cables for 6 binder head screw terminals (AWG 22...AWG 14)
Number of poles	2
Contacts type and composition	2(NC-NO), switch function: DPDT-DB
Contact form	Form ZZ
Contact operation	Snap action
Number of steps	1
Contacts material	Silver contacts
Positive opening	Without
Terminals description ISO n°1	(1-2)NC (3-4)NO (5-6)NC (7-8)NO
Minimum force for tripping	0.5 lbf
Maximum force for tripping	0.5 lbf
[I _e] rated operational current	0.1 A at 250 V DC

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

0.75 A at 480 V AC, B600 conforming to NEMA rating designation
 1.5 A at 240 V AC, B600 conforming to NEMA rating designation
 3 A at 120 V AC, B600 conforming to NEMA rating designation
 0.2 A at 125 V DC
 0.6 A at 600 V AC, B600 conforming to NEMA rating designation

[Ithe] conventional enclosed thermal current	10 A
[U] rated insulation voltage	600 V - for contact block (degree of pollution: 3) conforming to UL 508 600 V - for contact block conforming to CSA C22.2 No 14
Width	0.95 in
Height	2.5 in
Depth	2.54 in
Product weight	1.5 lb(US)

Environment

NEMA degree of protection	NEMA 1 conforming to Nema type 250
IP degree of protection	IP20 conforming to IEC 60529
Ambient air temperature for operation	-20...185 °F
Ambient air temperature for storage	-20...185 °F

Offer Sustainability

RoHS (date code: YYWW)	Will not be compliant Will not be compliant
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------