



### Main

Range of product	9007
Series name	Heavy duty
Product or component type	Limit switch
Product specific application	Hazardous location box
Device short name	9007CR
Body type	Fixed
Head type	Multi-directional head
Material	Metal
Fixing mode	By the body
Movement of operating head	Multi-directional
Type of operator	Acetal resin spring return wobble stick (-)
Switch actuation	By any moving part
Type of approach	Multi-directional approach multi-directional approach
Electrical connection	(AWG 22...AWG 12) screw-clamp terminals, 1...2
Cable entry	1 entry for 1/2" - 14 NPT conforming to ANSI B1.20.1
Number of poles	2
Contacts type and composition	2(NC-NO)
Contact operation	Snap action
Positive opening	Without
Level or class	Class I Division 1 Groups B/C/D Class II Division 1 Groups E/F/G
Sale per indivisible quantity	1

### Complementary

Body material	Aluminium
Head material	Zinc
Function available	2 stages sequential
Switch function	2 SPDT-DB
Contact form	Form Z
Contacts material	Silver contacts
Terminals description ISO n°1	(1-2)NC (3-4)NO

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

(5-6)NC  
(7-8)NO

Minimum torque for tripping	3 lbf.in
Tripping angle	10 °
Maximum displacement angle	90 °
[Ie] rated operational current	1.2 A at 600 V AC, A600 conforming to NEMA 1.5 A at 480 V AC, A600 conforming to NEMA 3 A at 240 V AC, A600 conforming to NEMA 6 A at 120 V AC, A600 conforming to NEMA 0.11 A at 250 V DC, R300 conforming to NEMA 0.55 A at 125 V DC, R300 conforming to NEMA
[Ithe] conventional enclosed thermal current	10 A
[Ui] rated insulation voltage	600 V degree of pollution 3 conforming to UL 508 for contact block 600 V degree of pollution 3 conforming to CSA C22.2 No 14 for contact block
[Uimp] rated impulse withstand voltage	2.5 kV AC for 1 min conforming to CE 2.2 kV AC for 1 min conforming to UL 2.64 kV AC for 1 s conforming to CSA
Short-circuit protection	10 A by CC fuse, protection type: non-time delay
Electrical durability	1000000 cycles
Local signalling	Without
Mechanical durability	10000000 cycles
Width	2.72 in
Height	10.35 in
Depth	2.08 in
Product weight	2.5 lb(US)

## Environment

Shock resistance	60 gn (duration = 9 ms) conforming to IEC 60068-2-27
Vibration resistance	25 gn (f = 10...150 Hz) conforming to IEC 60068-2-6
NEMA degree of protection	NEMA 2 conforming to Nema type 250 NEMA 4 conforming to Nema type 250 NEMA 6 conforming to Nema type 250 NEMA 6P conforming to Nema type 250 NEMA 12 conforming to Nema type 250 NEMA 13 conforming to Nema type 250 NEMA 1 conforming to Nema type 250
IP degree of protection	IP67 conforming to IEC 60529
Electrical shock protection class	Class 0 conforming to IEC 61140
Ambient air temperature for operation	-20...185 °F for hazardous location
Ambient air temperature for storage	-20...185 °F
Environmental characteristic	Standard environment
Protective treatment	Epoxy powder coat

## Offer Sustainability

RoHS (date code: YYWW)	Will not be compliant Will not be compliant
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

## Contractual warranty

Warranty period	18 months
-----------------	-----------