



### Main

Range of product	9012G
Pressure sensor type	Electromechanical pressure switch
Pressure sensor name	9012G
Pressure sensor size	675 psi
Maximum pressure	2000 psi
Contacts type and composition	NC-NO, SPDT-DB, Form Z, snap action, silver nickel contacts
Controlled fluid	Air Hydraulic oil (-40...250 °F) Non-corrosive liquids Non-corrosive gas
Fluid connection type	0.25 inch 18 NPTF conforming to UL 508
Pressure switch type of operation	Detection of 1 single threshold
Scale type	Fixed
Local display	With range scale window

### Complementary

Range on decreasing pressure	20...675 psi
Approx fix differential at mid range	27 psi +/- 2.5 % full scale
Cable entry	0.5 inch NPT conduit entrance
Terminal block type	4 screw terminals
Electrical connection	Screw-clamp terminals, AWG 22...AWG 12
Electrical circuit type	Control circuit
Local signalling	Without
[In] rated current	3 A (Ue = 240 V AC) contact code: A600 conforming to NEMA rating designation 6 A (Ue = 120 V AC) contact code: A600 conforming to NEMA rating designation 0.27 A (Ue = 250 V DC) contact code: R300 conforming to NEMA rating designation 0.22 A (Ue = 125 V DC) contact code: R300 conforming to NEMA rating designation
Setting	Internal
Enclosure material	Die cast aluminium alloy 380
Pressure actuator	Diaphragm (nitrile (Buna-N))
Height	5.45 in
Depth	2.63 in
Width	3.5 in

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Operating position	Any position
Materials in contact with fluid	Zinc plated steel Nitrile (Buna-N)
Short-circuit protection	10 A by gL (cartridge) overload and short-circuit protection
Operating rate	<= 120 cyc/mn
Mechanical durability	5000000 cycles
Repeat accuracy	4 %
Product weight	3 lb(US)

## Environment

Vibration resistance	2 gn conforming to IEC 68-2-6 (f = 40...150 Hz)
Shock resistance	50 gn conforming to IEC 58-2-27
Standards	CE UL 508 CSA C22.2 No 14
Product certifications	CE CSA LR25490 class 3211 03 UL listed file E12158 CCN NKPZ and CCN NTHT
NEMA degree of protection	NEMA 4/4X/13 conforming to UL 50
Ambient air temperature for operation	-10...185 °F

## Offer Sustainability

RoHS (date code: YYWW)	Will not be compliant <a href="#">Will not be compliant</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available <a href="#">Product Environmental Profile</a>
Product end of life instructions	Available <a href="#">End of Life Information</a>

## Contractual warranty

Warranty period	18 months
-----------------	-----------