



Main

Range of product	Square D Pumptrol
Pressure sensor name	9013GH
Pressure sensor size	250 psi (32...215 psi)
Value of setting	140...175 psi
Electrical circuit type	Power circuit
Product specific application	Control electrically driven water pumps and air compressors
Quantity per set	1
Type of packing	Individual

Complementary

Pressure sensor type	Electromechanical pressure switch
Controlled fluid	Air (-22...257 °F) Fresh water (-22...257 °F)
Adjustable range on rising pressure	80...250 psi
Approximate adjustable differential	24...45 psi
Destruction pressure	300 psi
Pressure actuator	Diaphragm
Pressure switch type of operation	Regulation between 2 thresholds
Scale type	Adjustable differential
Setting	Internal
Local display	Without
Contacts type and composition	2 NC, snap action, DPST-DB, Form YY
Cable entry number	3 knock-outs for 1/2" conduit UL 508
Electrical connection	Screw-clamp terminals, clamping capacity: 10 AWG Screw-clamp terminals, clamping capacity: 5.261 mm ²
Fluid connection type	0.375 inch NPSF internal conforming to UL 508
Short-circuit protection	20 A by cartridge fuse, type gG
Materials in contact with fluid	Zinc plated steel or equivalent flange Nitrile (Buna-N) or equivalent rubber diaphragm
Material	Polypropylene cover Noryl thermoplastic resin or equivalent cover
Operating position	Any position

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Motor power kW	1.5 kW (2 hp) at 115 V AC, 1 phase 2.2 kW (3 hp) at 115 V AC, 3 phases 2.2 kW (3 hp) at 230 V AC, 1 phase 0.75 kW (1 hp) at 115 V DC 0.75 kW (1 hp) at 230 V DC 3.75 kW (5 hp) at 230 V AC, 3 phases 3.7 kW (5 hp) at 460 V AC, 1 phase 3.7 kW (5 hp) at 460 V AC, 3 phases 3.7 kW (5 hp) at 575 V AC, 1 phase 3.7 kW (5 hp) at 575 V AC, 3 phases
Electrical durability	100000 cycles at 10 cyc/mn
Mechanical durability	300000 cycles
Terminal block type	4 terminals
Operating rate	10 cyc/mn
[Ui] rated insulation voltage	575 V conforming to UL 508
Product weight	2.25 lb(US)
Repeat accuracy	+/- 3 %
Terminals description ISO n°1	L1-T1 L2-T2
Width	4.19 in
Height	5.4 in
Depth	3.88 in
Factory modification	2-way pressure release valve

Environment

Standards	CE UL 508 NSF ANSI 372
Ambient air temperature for operation	-33...257 °F
Ambient air temperature for storage	-33...257 °F
Protective treatment	None
NEMA degree of protection	NEMA 1 conforming to UL 50
IP degree of protection	IP20 conforming to IEC 60529
Product certifications	UL listed file E12158 CSA file LR25490

Offer Sustainability

RoHS (date code: YYWW)	Will not be compliant Will not be compliant
REACH	Reference contains SVHC above the threshold - Go to CaP for more details Go to CaP for more details
Product environmental profile	Available Product Environmental Profile
Product end of life instructions	Available End of Life Information

Contractual warranty

Warranty period	18 months
-----------------	-----------