

# Product data sheet

Specifications



## Remote indication auxiliary, Acti9 iACTs, 2 NO

A9C15916

### Main

Range Of Product	ICT
Range	Acti9
Device Short Name	iACTs
Product Or Component Type	Remote indication auxiliary
Signal Contacts Composition	2 NO

### Complementary

Signalling Circuit Voltage	24 V AC/DC: 10 mA 230 V AC: 50/60 Hz 5 A 230 V AC: 50/60 Hz 2 A 130 V DC: 1 A
[Uc] Control Circuit Voltage	24...240 V AC 50/60 Hz 24...130 V DC
Range Compatibility	Acti 9 Acti9 iCT
[Ui] Rated Insulation Voltage	440 V
[Uimp] Rated Impulse Withstand Voltage	4 kV
Mounting Mode	Fixed, on the right of CT
Mounting Support	35 mm symmetrical DIN rail
9 Mm Pitches	1
Height	81 mm
Width	9 mm
Depth	68 mm
Colour	White
Auxiliary Connection Terminal	Tunnel type terminals2 cable(s) flexible 2.5 mm² Tunnel type terminals2 cable(s) rigid 1.5 mm² Tunnel type terminals1 cable(s) rigid 1.5...2.5 mm² Tunnel type terminals1 cable(s) flexible 1.5...2.5 mm²
Wire Stripping Length	9 mm
Tightening Torque	0.8 N.m
Product Compatibility	ICT
Market Segment	Residential Small commercial
Compatibility Code	iACTs

### Environment

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Standards	EN 60947-5
Ip Degree Of Protection	IP20 IP20 conforming to IEC 60529
Tropicalisation	2
Relative Humidity	95 % at 55 °C
Ambient Air Temperature For Operation	-20...50 °C
Ambient Air Temperature For Storage	-40...70 °C

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7.7 cm
Package 1 Width	2.1 cm
Package 1 Length	8.8 cm
Package 1 Weight	43.0 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	8.0 cm
Package 2 Width	9.5 cm
Package 2 Length	23.0 cm
Package 2 Weight	502.0 g
Unit Type Of Package 3	S03
Number Of Units In Package 3	120
Package 3 Height	30.0 cm
Package 3 Width	30.0 cm
Package 3 Length	40.0 cm
Package 3 Weight	6.366 kg

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability






**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

## Well-being performance

	Reach Free Of Svhc	
	Toxic Heavy Metal Free	
	Mercury Free	
	Rohs Exemption Information	<a href="#">Yes</a>
	Halogen Free Product	
Reach Regulation		<a href="#">REACH Declaration</a>
Eu Rohs Directive		Compliant <a href="#">EU RoHS Declaration</a>
China Rohs Regulation		<a href="#">China RoHS declaration</a>
Weee		The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins