



### Main

Range of product	Acti 9
Product name	Acti 9 iPRD
Product or component type	Surge arrester with pluggable cartridge
Device short name	IPRD8
Device application	Distribution
Poles description	1P + N
Remote signalling	Without
Surge arrester type	Electrical distribution network
Earthing system	TN-S TT
[Uoc] open circuit voltage	10 kV type 3 common mode N/PE 10 kV type 3 differential mode L/N

### Complementary

Surge arrester class type	Type 2 + 3
Surge arrester technology	MOV + GDT
[Ue] rated operational voltage	230 V (+/- 10 %) AC 50/60 Hz 400 V (+/- 10 %) AC 50/60 Hz
[In] nominal discharge current	Common mode : 2.5 kA L/PE Common mode : 2.5 kA N/PE Differential mode : 2.5 kA L/N
[Imax] maximum discharge current	Common mode : 8 kA L/PE Common mode : 8 kA N/PE Differential mode : 8 kA L/N
[Uc] maximum continuous operating voltage	Common mode : 260 V N/PE Common mode : 350 V L/PE Differential mode : 350 V L/N
[Up] voltage protection level	<= 1.4 kV type 2 common mode N/PE <= 1.1 kV type 3 common mode N/PE <= 1 kV type 2 differential mode L/N <= 1.1 kV type 3 differential mode L/N
[Ut] temporary overvoltage	Withstand : 337 V L/N for 5 s Withstand : 442 V L/PE for 5 s

Safe failure mode : 1200 V N/PE for 200 ms

Disconnecter device type	Associated circuit breaker iC60H 10 A curve C - Icu 15 kA Associated circuit breaker iC60L 10 A curve C - Icu 25 kA Associated circuit breaker iC60N 10 A curve C - Icu 10 kA
[Iscsr] short-circuit current rating	50 kA
Mounting mode	Clip-on
Mounting support	DIN rail
9 mm pitches	4
Height	85 mm
Width	36 mm
Depth	69 mm
Product weight	0.211 kg
Colour	White ( RAL 9003 )
Response time	<= 25 ns
[Ipe] Ground residual current	0.6 mA 0.003 mA
Connections - terminals	Tunnel type terminal, downside 2.5...35 mm <sup>2</sup> Tunnel type terminal, upside 2.5...35 mm <sup>2</sup>
Tightening torque	2.5 N.m

## Environment

Standards	EN 61643-11 : 2012 IEC 61643-11 : 2011
Product certifications	CE
Quality labels	NF KEMA-KEUR
IP degree of protection	On front face : IP40 conforming to IEC 60529 Built-in : IP20 conforming to IEC 60529
IK degree of protection	IK03 conforming to IEC 62262
Relative humidity	5...95 %
Operating altitude	2000 m
Ambient air temperature for operation	-25...60 °C
Ambient air temperature for storage	-40...85 °C

## Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0844 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available <a href="#">Product Environmental Profile</a>
Product end of life instructions	Available <a href="#">End of Life Information</a>

## Contractual warranty

Warranty period	18 months
-----------------	-----------