

Product data sheet

Specifications



iPF K 20 modular surge arrester - 3 poles - 340V

A9L15597

Main

Range Of Product	Acti9
Product Name	Acti9 iPF K
Product Or Component Type	Surge arrester
Device Short Name	iPF K
Device Application	Distribution
Standards	IEC 61643-11:2011
Product Certifications	CE EAC
Poles Description	3P
Remote Signalling	Without
Surge Arrester Type	Electrical distribution network
Earthing System	TN-C IT 230

Complementary

Surge Arrester Class Type	Type 2
Surge Arrester Technology	MOV
[Ue] Rated Operational Voltage	230/400 V AC (+/- 10 %) at 50/60 Hz
[In] Nominal Discharge Current	Common mode: 5 kA (L/PE) Common mode: 5 kA (N/PE)
[Imax] Maximum Discharge Current	Common mode: 20 kA L/PE
[Uc] Maximum Continuous Operating Voltage	Common mode: 340 V L/PE
Maximum [Up] Voltage Protection Level	Common mode <1.1 kV type 2 L/PE
[Ut] Temporary Overvoltage	337 V L/N 5 s withstand 442 V L/PE 5 s withstand 1200 V N/PE 200 ms withstand 1453 V L/PE 200 ms withstand
Disconnecter Device Type	Associated circuit breaker iK60N 20 A curve C - Icu 6 kA Associated fuse gG 25 A - Icu 25 kA
Signalling Circuit Voltage	0.25 A/250 V AC 50/60 Hz
Mounting Mode	Clip-on (DIN rail)
9 Mm Pitches	8
Height	81 mm
Width	72 mm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Depth	69 mm
Net Weight	335 g
Colour	White (RAL 9003)
[Ipe] Ground Residual Current	25 mA
Connections - Terminals	Tunnel type terminal (top or bottom) 25 mm² rigid Tunnel type terminal (top or bottom) 16 mm² flexible Tunnel type terminal (top or bottom) 16 mm² flexible with ferrule
Wire Stripping Length	11 mm
Tightening Torque	3.5 N.m

Environment

Ik Degree Of Protection	IK03 conforming to IEC 62262
Relative Humidity	5...95 %
Operating Altitude	2000 m
Ambient Air Temperature For Operation	-25...60 °C
Ambient Air Temperature For Storage	-40...85 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7.5 cm
Package 1 Width	8.0 cm
Package 1 Length	8.5 cm
Package 1 Weight	360.0 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	3
Package 2 Height	10.0 cm
Package 2 Width	9.0 cm
Package 2 Length	28.0 cm
Package 2 Weight	1.082 kg
Unit Type Of Package 3	S03
Number Of Units In Package 3	36
Package 3 Height	30.0 cm
Package 3 Width	30.0 cm
Package 3 Length	40.0 cm
Package 3 Weight	13.426 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information