

# Product data sheet

Specifications



## iQuick PRD8r modular surge arrester - 1 pole + N - 350V - with remote transfer

A9L16298

### Main

Range Of Product	Acti9
Product Name	Acti9 iQuick PRD
Product Or Component Type	Surge arrester with pluggable cartridge
Device Short Name	iQuick PRD8r
Device Application	Distribution
Standards	EN 61643-11:2012 IEC 61643-11:2011
Product Certifications	CE
Quality Labels	NF KEMA-KEUR
Poles Description	1P + N
Remote Signalling	With
Signal Contacts Composition	1 SD (1 C/O)
Surge Arrester Type	Electrical distribution network
Earthing System	TN-S TT

### Complementary

Surge Arrester Class Type	Type 2 + 3
Surge Arrester Technology	MOV + GDT
[Ue] Rated Operational Voltage	230 V AC (+/- 10 %) at 50/60 Hz
[In] Nominal Discharge Current	Common mode: 2 kA (L/PE) Common mode: 2 kA (N/PE) Differential mode: 2 kA (L/N)
[Imax] Maximum Discharge Current	Common mode: 8 kA L/PE Common mode: 8 kA N/PE Differential mode: 8 kA L/N
[Uoc] Open Circuit Voltage	10 kV type 3 common mode L/PE 10 kV type 3 common mode N/PE 10 kV type 3 differential mode L/N
[Uc] Maximum Continuous Operating Voltage	Common mode: 264 V N/PE Common mode: 350 V L/PE Differential mode: 350 V L/N
Maximum [Up] Voltage Protection Level	Common mode <1.5 kV type 2 L/PE Common mode <1.7 kV type 2 N/PE Differential mode <1.2 kV type 2 L/N Common mode <1.4 kV type 3 L/PE Differential mode <1.4 kV type 3 L/N Common mode <1.5 kV type 3 N/PE

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Disconnecter Device Type	Integrated circuit breaker - Icu 25 kA
Signalling Circuit Voltage	2 A/250 V AC 50/60 Hz
Mounting Mode	Clip-on (DIN rail)
9 Mm Pitches	8
Height	94 mm
Width	72 mm
Depth	75.9 mm
Net Weight	0.43 kg
Colour	White (RAL 9003)
Connections - Terminals	Tunnel type terminal (downside) 2.5...25 mm² Tunnel type terminal (upside) 2.5...25 mm²
Tightening Torque	2.5 N.m

## Environment

Ik Degree Of Protection	IK05 conforming to IEC 62262
Relative Humidity	5...95 %
Operating Altitude	2000 m
Ambient Air Temperature For Operation	-25...60 °C
Ambient Air Temperature For Storage	-40...70 °C

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	9.0 cm
Package 1 Width	9.0 cm
Package 1 Length	10.0 cm
Package 1 Weight	488.0 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	27
Package 2 Height	30.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	13.889 kg

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™** label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance



Mercury Free



RoHS Exemption Information

[Yes](#)



Halogen Free Plastic Parts & Cables  
Product

## Certifications & Standards

Reach Regulation

[REACH Declaration](#)

Eu RoHS Directive

Compliant with Exemptions

China RoHS Regulation

[China RoHS declaration](#)

Product out of China RoHS scope. Substance declaration for your information

Environmental Disclosure

[Product Environmental Profile](#)

Weee

The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Circularity Profile

No need of specific recycling operations