



Main

Product or component type	Cartridge
Device short name	C neutral PV
Surge arrester type	Electrical distribution network

Complementary

Surge arrester class type	Type 2
Surge arrester technology	GDT
[Ue] rated operational voltage	600 V DC
Nominal discharge current	20 kA
Maximum discharge current	65 kA
[Uc] maximum continuous operating voltage	260 V
[Up] voltage protection level	1.4 kV type 2
Local signalling	Flag color: white/red
Mounting mode	Plug-in
Mounting support	Into SPD module
9 mm pitches	2
Height	50 mm
Width	18 mm
Depth	60 mm
Colour	White (RAL 9003)
Material	PBT (polybutylene terephthalate)
Response time	< 25 ns

Environment

Standards	EN 61643-11 IEC 61643-1
IP degree of protection	Front face : IP20
Relative humidity	5...90 %

Operating altitude	0...2000 m
Ambient air temperature for operation	-25...60 °C
Ambient air temperature for storage	-40...85 °C

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0627 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference contains SVHC above the threshold - Go to CaP for more details Go to CaP for more details
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------