

# Product data sheet

Specifications



## energy sensor, PowerTag Flex 230V 63A 1P+N top and bottom position

A9MEM1560

### Main

Range Of Product	PowerLogic
Product Name	PowerTag A9 F63
Product Or Component Type	Energy sensor
Poles	1P + N
Maximum Current [Imax]	63 A
[Ib] Basic Current	10 A
Starting Current	40 mA
Saturation Current	130 A
Product Specific Application	Cost allocation Load monitoring Circuit monitoring Overload alarm Energy management
Concentrator Compatibility	Acti9 Smartlink SI B Acti9 Smartlink SI D Acti9 PowerTag Link C Acti9 PowerTag Link Acti9 PowerTag Link HD Harmony Hub Wiser IP module EcoStruxure Panel Server Universal EcoStruxure Panel Server Advanced PrismaSet Active
Range Compatibility	Acti 9 Acti9 iCV40 Acti 9 Vigi iC40 Acti 9 Vigi iC60 Acti 9 Acti9 iDD40 XA Acti 9 Acti9 iCV40 XA Acti 9 Vigi iDT40
Type Of Measurement	Active energy Current Voltage Power factor Active power
Accuracy Class	Class 1 current conforming to IEC 61557-12 Class 0.5 voltage conforming to IEC 61557-12 Class 1 active power conforming to IEC 61557-12 Class 1 active energy conforming to IEC 61557-12 Class 1 power factor conforming to IEC 61557-12
Mounting Location	Top or bottom
Mounting Support	On circuit breaker
Product Destination	Switchboard
Event Management	Voltage loss with measured current at voltage loss
Transmission Support Medium	Radio frequency 2.4...2.4835 GHz conforming to IEEE 802.15.4

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Emission Power	10 mW
----------------	-------

## Complementary

Mounting Mode	By screws (terminals)
Electrical Connection (Voltage Sensing & Power Supply)	Wires with cable end
Cable Cross Section	1 rigid cable 1.5...16 mm² 2 stranded cable 1.5...2.5 mm² 2 rigid cable 1.5...2.5 mm² 1 stranded cable 1.5...16 mm²
Cable Length	0.25 m
Supply Voltage	200...240 V AC, +/- 20 %
Cable Composition	1 x 0.33 mm²
Network Frequency	50 Hz 60 Hz
Maximum Power Consumption	1 VA
Standards	IEC 61557-12 IEC 61010-1 IEC 61010-2-030 IEC 61326-1 ETSI EN 300 328 ETSI EN 301 487-1
Height	Sensor element: 20 mm
Width	Sensor element: 18 mm
Depth	Sensor element: 44.5 mm
Net Weight	16 g
Colour	White (RAL 9003)

## Environment

Quality Labels	CE
Directives	2014/53/EU - radio equipment directive
Operating Altitude	0...2000 m
Ambient Air Temperature For Operation	-25...60 °C
Ambient Air Temperature For Storage	-40...85 °C
Overvoltage Category	III conforming to IEC 61010-1
Measurement Category	Category III conforming to IEC 61010-2-030
Ip Degree Of Protection	IP20 conforming to IEC 60529
Ik Degree Of Protection	IK05
Pollution Degree	3
Relative Humidity	0...95 % at 45 °C conforming to IEC 60721-3-3
Vibration Resistance	3M4 conforming to IEC 60721-3-3
Electromagnetic Compatibility	Industrial electromagnetic environment conforming to IEC 61326-1 Radiated EMC conforming to ETSI EN 301 489-17 Electromagnetic emission conforming to IEC 62311
Environmental Characteristics	Dustproof class 3S3 conforming to IEC 60721-3-3 Salt mist class 3C2 conforming to IEC 60721-3-3 Indoor use

# Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.000 cm
Package 1 Width	6.000 cm
Package 1 Length	8.500 cm
Package 1 Weight	44.000 g
Unit Type Of Package 2	S02
Number Of Units In Package 2	48
Package 2 Height	15.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	2.463 kg

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance



Mercury Free



RoHS Exemption Information

Yes

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	<a href="#">End of Life Information</a>
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>