



Main

Range of product	Acti 9
Product name	Acti 9 CT
Product or component type	Contacteur
Device short name	CT
Device application	Control circuit
Poles	2P
[Ie] rated operational current	25 A AC-7A 8.5 A AC-7B
Pole contact composition	2 NO
Network type	AC
Utilisation category	AC-1 conforming to IEC 60947-4
Control type	Remote control
[Uc] control circuit voltage	230 V AC 50 Hz

Complementary

Network frequency	50/60 Hz
[Ue] rated operational voltage	250 V AC 50 Hz
Maximum power	3 W at 250 V AC
[Ui] rated insulation voltage	500 V AC
[Uimp] rated impulse withstand voltage	2.5 kV
Control signal type	Maintained
Switching frequency	100 switching operations/day
Local signalling	Color indicator
Hold-in power consumption in VA	3.8 VA
Inrush power in VA	15 VA
Mounting mode	Clip-on
Mounting support	35 mm symmetrical DIN rail
9 mm pitches	2
Height	90 mm

Width	18 mm
Depth	66 mm
Net weight	110 g
Colour	White
Connections - terminals	Power circuit: tunnel type terminals2 cable(s) 2.5 mm ² flexible Power circuit: tunnel type terminals1 cable(s) 6 mm ² rigid Control circuit: tunnel type terminals2 cable(s) 2.5 mm ² flexible Control circuit: tunnel type terminals2 cable(s) 1.5 mm ² rigid
Tightening torque	0.8 N.m
Wire stripping length	10 mm
Product compatibility	No auxiliary
Compatibility code	CT

Environment

Standards	IEC 61095 EN 61095
Product certifications	NF
Noise level	30 dB
IP degree of protection	IP20 conforming to IEC 60529 IP40 (modular enclosure) conforming to IEC 60529
Pollution degree	2
Tropicalisation	2 conforming to CEI 61095 2 conforming to EN 61095
Relative humidity	95 % at 55 °C
Operating altitude	2000 m
Ambient air temperature for operation	-5...60 °C
Ambient air temperature for storage	-40...60 °C

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Under investigation
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
----------	-----------