



Main

Range of product	Acti 9
Product name	Acti 9 iCT
Product or component type	Contactor
Device short name	ICT
Device application	Motor-heating-lighting
Poles	2P
[Ie] rated operational current	6 A AC-7B 16 A AC-7A
Pole contact composition	2 NO
Network type	AC
Control type	Remote control
[Uc] control circuit voltage	24 V AC 50 Hz

Complementary

Network frequency	50 Hz
[Ue] rated operational voltage	250 V AC 50 Hz
Maximum power	1.3 W 250 V AC
[Ui] rated insulation voltage	500 V AC 50/60 Hz
[Uimp] rated impulse withstand voltage	4 kV
Control signal type	Maintained
Switching frequency	100 switching operations/day
Local signalling	Action indicator
Hold-in power consumption in VA	3.8 VA
Inrush power in VA	15 VA
Mounting mode	Clip-on
Mounting support	35 mm symmetrical DIN rail
9 mm pitches	2
Height	81 mm
Width	18 mm

Depth	60 mm
Colour	White
Mechanical durability	1000000 cycles
Electrical durability	30000 cycles, 50 Hz, AC-7C conforming to IEC/EN 61095 100000 cycles, 50 Hz, AC-1 conforming to EN/IEC 60947-4-1 30000 cycles, 50 Hz, AC-3 conforming to EN/IEC 60947-4-1 30000 cycles, 50 Hz, AC-5A conforming to EN/IEC 60947-4-1 30000 cycles, 50 Hz, AC-5B conforming to EN/IEC 60947-4-1 100000 cycles at 16 A, 50 Hz, AC-7A conforming to IEC/EN 61095 30000 cycles at 6 A, 50 Hz, AC-7B conforming to IEC/EN 61095
Connections - terminals	Control circuit : 2 tunnel type terminals 1.5 mm ² for rigid cable(s) Power circuit : 1 tunnel type terminals 1...4 mm ² for flexible cable(s) Power circuit : 1 tunnel type terminals 1.5...6 mm ² for rigid cable(s) Control circuit : 1 tunnel type terminals 1.5...2.5 mm ² for rigid cable(s) Control circuit : 2 tunnel type terminals 1.5...2.5 mm ² for flexible cable(s)
Tightening torque	Control circuit : 0.8 N.m Power circuit : 0.8 N.m
Product compatibility	IACTs

Environment

Standards	IEC/EN 61095
Noise level	30 dB
Heat dissipation	1.3 W
IP degree of protection	IP20
Pollution degree	2
Tropicalisation	2 conforming to EN 60947-4-1 2 conforming to EN 61095 2 conforming to IEC 1095
Relative humidity	95 % (55 °C)
Operating altitude	2000 m
Ambient air temperature for operation	-5...60 °C
Ambient air temperature for storage	-40...70 °C

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0627 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available Product Environmental Profile
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------