



Main

Range	Prodis
Product or component type	Add-on residual current devices
Device short name	Vigi DT40
Poles description	3P + N
Neutral position	Left
[In] rated current	40 A
Network type	AC
Earth-leakage sensitivity	300 mA
Earth-leakage protection time delay	Instantaneous
Earth-leakage protection class	Type AC

Complementary

Device location in system	Outgoer
Network frequency	50 Hz
[Ue] rated operational voltage	400 V AC 50 Hz phase to phase
Residual current tripping technology	Voltage independent
[Ui] rated insulation voltage	400 V AC 50 Hz conforming to EN 61009-1
[Uimp] rated impulse withstand voltage	6 kV conforming to EN 61009-1
Local signalling	ON/OFF indication
Mounting mode	Clip-on
Mounting support	DIN rail
Electrical connection to mcb	By screws
9 mm pitches	4
Height	81 mm
Width	54 mm
Depth	69 mm
Net weight	210 g

Colour	White
Electrical durability	10000 cycles
Connections - terminals	Cable downstream 0.75...16 mm ² rigid Cable downstream 0.33...10 mm ² flexible
Wire stripping length	13 mm
Tightening torque	2 N.m

Environment

Standards	EN 61009-1 EN 61009-2-1
IP degree of protection	IP20 conforming to IEC 60529
Pollution degree	3 conforming to EN 61009-1
Tropicalisation	2 conforming to IEC 60068-1
Relative humidity	95 % at 55 °C
Operating altitude	2000 m
Ambient air temperature for operation	-5...60 °C
Ambient air temperature for storage	-40...60 °C

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Under investigation
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
----------	-----------