

Product data sheet

Specifications



Voltage release MSU 275VAac dc

A9N26979

⚠ Discontinued on: Apr 29, 2019

⚠ Discontinued

Main

Range Of Product	Librio Prodis Acti9 Clario
Product Or Component Type	Overvoltage release
Device Short Name	MSU
[Uc] Control Circuit Voltage	230 V AC 50 Hz
Threshold Tripping Voltage	275 V
9 Mm Pitches	2

Complementary

Range Compatibility	Acti 9 Acti9 iDPN Acti 9 Acti9 C120 Acti 9 Acti9 C40 Acti 9 Acti9 C60H-DC Acti 9 Acti9 C60NA-DC Acti 9 Acti9 C60PV-DC Acti 9 Acti9 DPN Vigi Acti 9 Acti9 DT40 Acti 9 Acti9 DT60 Acti 9 Acti9 ID C40 Acti 9 Acti9 IDc Acti 9 Acti9 ITG40 Acti 9 Acti9 ID Acti 9 Acti9 DPN
Local Signalling	Action indicator
Mounting Mode	Fixed
Mounting Support	35 mm symmetrical DIN rail
Height	82.5 mm
Width	18 mm
Depth	68 mm
Colour	White
Connections - Terminals	Clamp terminal - 1 cable(s) 2.5 mm² - flexible
Wire Stripping Length	9 mm
Tightening Torque	1 N.m

Environment

Standards	EN/IEC 60947-5-1
-----------	------------------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Product Certifications	ASTA KEMA ASEFA LCIE
Tropicalisation	2 conforming to EN/IEC 60947-5-1
Relative Humidity	95 % at 55 °C
Ambient Air Temperature For Operation	-25...50 °C
Ambient Air Temperature For Storage	-40...85 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.8 cm
Package 1 Width	8 cm
Package 1 Length	9.5 cm
Package 1 Weight	0.077 kg

Contractual warranty

Warranty	18 months
----------	-----------