

Product data sheet

Specifications



2 ways low level switch iCME 10 A
0,1..5 CA 0,05..3 CCA 2P U 1..440
VAC/VCCV CA

A9E15122

Main

Range Of Product	Acti9
Product Name	Acti9 iCM
Product Or Component Type	Selector switch
Device Short Name	iCME
Device Application	Electrical circuit control
Contacts Type And Composition	1 NO + 1 NC
Standards	EN 60947-3 IEC 60947-3 VDE 0660 part 107 UL

Complementary

Maximum Operating Voltage	440 V
Control Type	Rotary handle 2 positions
Marking	1 - 2
Mounting Mode	Clip-on
Mounting Support	DIN rail
9 Mm Pitches	4
Height	60 mm
Width	36 mm
Depth	75 mm
Net Weight	44 g
Colour	White
Mechanical Durability	1000000 cycles
Electrical Durability	AC-21A: 200000 cycles
Connections - Terminals	Jumper terminals1.5 mm²
Wire Stripping Length	9 mm for downside connection
Tightening Torque	1 N.m downside

Environment

Ip Degree Of Protection	IP20 conforming to IEC 60529
Ambient Air Temperature For Operation	-20...55 °C
Ambient Air Temperature For Storage	-25...80 °C

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.3 cm
Package 1 Width	7.6 cm
Package 1 Length	8.4 cm
Package 1 Weight	68 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	80
Package 2 Height	30 cm
Package 2 Width	30 cm
Package 2 Length	40 cm
Package 2 Weight	5.958 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

Well-being performance

	Reach Free Of Svhc	
	Toxic Heavy Metal Free	
	Mercury Free	
	Rohs Exemption Information	Yes
Reach Regulation	REACH Declaration	
Eu Rohs Directive	Compliant	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)	
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins	