

Product data sheet

Specifications



Acti9 - iDPN N Arc - 1P+N 25A C 6000A - Arc fault detection circuit breaker

A9FDB625

Main

Range	Acti9
Product Name	Acti9 iDPN N Arc
Product Or Component Type	Arc fault detection circuit breaker
Product Specific Application	Fire prevention by arc detection
Standards	EN/IEC 62606 IEC 60898-1
Device Short Name	iDPN N Arc
Poles Description	1P + N
[In] Rated Current	25 A at 30 °C
Curve Code	C
Breaking Capacity	6000 A Icn at 230 V AC 50 Hz conforming to EN/IEC 60898-1
Network Type	AC
Neutral Position	Left
Trip Unit Technology	Thermal-magnetic

Complementary

Number Of Protected Poles	1
Network Frequency	50 Hz
[Ue] Rated Operational Voltage	230 V AC 50 Hz conforming to IEC 62606 230 V AC 50 Hz conforming to EN/IEC 60898-1
Device Location In System	Outgoer
Magnetic Tripping Limit	5...10 x In
Limitation Class	3 conforming to IEC 60898-1
Threshold Tripping Voltage	400 V 200 ms
[Uimp] Rated Impulse Withstand Voltage	4 kV conforming to IEC 60898-1
[Ui] Rated Insulation Voltage	400 V AC
Contact Position Indicator	Yes
Control Type	Toggle
Local Signalling	ON, OFF, fault trip
Mounting Mode	Clip-on
Mounting Support	DIN rail
Colour	White

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Mechanical Durability	20000 cycles
Electrical Durability	10000 cycles 230 V AC 50 Hz
Overvoltage Category	III
Cable Entry	Top
Connections - Terminals	Tunnel type terminal for 1 cable(s) 10 mm² flexible Tunnel type terminal for 2 cable(s) 2.5 mm² flexible Tunnel type terminal for 1 cable(s) 16 mm² rigid Tunnel type terminal for 2 cable(s) 2.5 mm² rigid
Wire Stripping Length	14 mm
Tightening Torque	2 N.m
Comb Busbar And Distribution Block Compatibility	ProDis Librio
Connection Pitch	9 mm between phase and neutral
9 Mm Pitches	4
Height	81 mm
Width	36 mm
Depth	72 mm
Net Weight	190 g

Environment

Heat Dissipation	7.24 W at 230 V - 25 A
Ip Degree Of Protection	IP20
Pollution Degree	2
Tropicalisation	Severity B conforming to IEC 60068-2-30 for 28 d
Operating Altitude	2000 m
Ambient Air Temperature For Operation	-25...60 °C
Ambient Air Temperature For Storage	-40...85 °C
Product Certifications	RCM

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8.9 cm
Package 1 Width	4.0 cm
Package 1 Length	10.0 cm
Package 1 Weight	139.0 g
Unit Type Of Package 2	S02
Number Of Units In Package 2	8
Package 2 Height	15.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	1.567 kg

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Sustainable Packaging Transparency RoHS/REACH

Resource performance

 Sustainable Packaging

Well-being performance

 Mercury Free

 Rohs Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information