



Main

Range of product	Acti 9
Product name	Acti 9 iPRD
Product or component type	Surge arrester with pluggable cartridge
Device short name	IPRD8
Device application	Distribution
Poles description	3P
Remote signalling	Without
Surge arrester type	Electrical distribution network
Earthing system	TN-C
[Uoc] open circuit voltage	10 kV type 3 common mode L/PE

Complementary

Surge arrester class type	Type 2 + 3
Surge arrester technology	MOV
[Ue] rated operational voltage	230/400 V (+/- 10 %) AC 50/60 Hz
[In] nominal discharge current	Common mode : 2.5 kA L/PE
[Imax] maximum discharge current	Common mode : 8 kA L/PE
[Uc] maximum continuous operating voltage	Common mode : 350 V L/PE
[Up] voltage protection level	<= 1.2 kV type 2 common mode L/PE <= 1.2 kV type 3 common mode L/PE
[Ut] temporary overvoltage	Withstand : 337 V L/N for 5 s Safe failure mode : 1200 V N/PE for 200 ms Withstand : 422 V L/PE for 720 ms Safe failure mode : 1455 V L/PE for 200 ms
Disconnecter device type	Associated circuit breaker iC60H 10 A curve C - Icu 15 kA Associated circuit breaker iC60L 10 A curve C - Icu 25 kA Associated circuit breaker iC60N 10 A curve C - Icu 10 kA
[Iscsr] short-circuit current rating	50 kA
Mounting mode	Clip-on
Mounting support	DIN rail

9 mm pitches	6
Height	85 mm
Width	54 mm
Depth	69 mm
Product weight	340 g
Colour	White (RAL 9003)
Response time	<= 25 ns
[Ipe] Ground residual current	0.6 mA
Connections - terminals	Tunnel type terminal, top or bottom 2.5...25 mm ² cable(s) rigid Tunnel type terminal, top or bottom 4...16 mm ² cable(s) flexible Tunnel type terminal, top or bottom 4...16 mm ² cable(s) flexible with ferrule
Tightening torque	3.5 N.m

Environment

Standards	EN 61643-11 : 2012 IEC 61643-11 : 2011
Product certifications	CE
Quality labels	NF KEMA-KEUR
IP degree of protection	On front face : IP40 conforming to IEC 60529 Built-in : IP20 conforming to IEC 60529
IK degree of protection	IK03 conforming to IEC 62262
Relative humidity	5...95 %
Operating altitude	2000 m
Ambient air temperature for operation	-25...60 °C
Ambient air temperature for storage	-40...85 °C

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0844 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available Product Environmental Profile
Product end of life instructions	Available End of Life Information

Contractual warranty

Warranty period	18 months
-----------------	-----------