



### Main

Range of product	Acti 9
Product name	Acti 9 iQuick PRD
Product or component type	Surge arrester with pluggable cartridge
Device short name	IQuick PRD
Device application	Distribution
Poles description	1P + N
Remote signalling	With
Signal contacts composition	1 SD (1 C/O)
Surge arrester type	Electrical distribution network
Earthing system	TN-S TT

### Complementary

Surge arrester class type	Type 2
Surge arrester technology	MOV + GDT
[Ue] rated operational voltage	230 V (+/- 10 %) AC 50/60 Hz
[In] nominal discharge current	Common mode : 20 kA L/PE Common mode : 20 kA N/PE Differential mode : 20 kA L/N
[Imax] maximum discharge current	Common mode : 40 kA L/PE Common mode : 40 kA N/PE Differential mode : 40 kA L/N
[Uc] maximum continuous operating voltage	Common mode : 264 V N/PE Common mode : 350 V L/PE Differential mode : 350 V L/N
[Up] voltage protection level	<= 1.5 kV type 2 common mode L/PE <= 1.5 kV type 2 common mode N/PE <= 2.5 kV type 2 differential mode L/N
Disconnecter device type	Integrated circuit breaker - Icu 20 kA
[Iscrr] short-circuit current rating	20 kA

Signalling circuit voltage	2 A/250 V AC 50/60 Hz
Mounting mode	Clip-on
Mounting support	DIN rail
9 mm pitches	8
Height	94 mm
Width	72 mm
Depth	75.9 mm
Product weight	0.44 kg
Colour	White ( RAL 9003 )
Response time	<= 25 ns
Connections - terminals	Tunnel type terminal, downside 2.5...25 mm <sup>2</sup> Tunnel type terminal, upside 2.5...35 mm <sup>2</sup>
Tightening torque	2.5 N.m

## Environment

Standards	EN 61643-11 : 2012 IEC 61643-11 : 2011
Product certifications	CE
Quality labels	NF KEMA-KEUR
IP degree of protection	On front face : IP40 conforming to IEC 60529 Built-in : IP20 conforming to IEC 60529
IK degree of protection	IK05 conforming to IEC 62262
Relative humidity	5...90 %
Operating altitude	2000 m
Ambient air temperature for operation	-25...60 °C
Ambient air temperature for storage	-40...70 °C

## Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1742 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available <a href="#">Product Environmental Profile</a>
Product end of life instructions	Need no specific recycling operations

## Contractual warranty

Warranty period	18 months
-----------------	-----------