

Product data sheet

Specifications



iPRD-DC 40r 1000PV modular surge arrester - 2P - 1000VDC with remote transfer

A9L16436

⚠ Discontinued on: Mar 31, 2022

⚠ Discontinued

Main

Range Of Product	Acti9
Product Name	Acti9 iPRD-DC
Device Short Name	iPRD-DC
Product Or Component Type	Surge arrester with pluggable cartridge
Poles Description	2P
Output Type	Contact (volt-free)
Signal Contacts Composition	1 SD (1 C/O)
Surge Arrester Type	Electrical distribution network

Complementary

Surge Arrester Class Type	Type 2
Surge Arrester Technology	MOV
[Ue] Rated Operational Voltage	1000 V +/- 10 % DC
[In] Nominal Discharge Current	15 kA
[Imax] Maximum Discharge Current	40 kA
[Ucpv] Maximum Continuous Operating Voltage	Differential mode: 1000 V L+/L- Common mode: 1000 V L+/PE Common mode: 1000 V L-/PE
Maximum [Up] Voltage Protection Level	Common mode <3.9 kV type 2 L+/PE Common mode <3.9 kV type 2 L-/PE Differential mode <3.9 kV type 2 L+/L-
Disconnecter Device Type	Integrated disconnecter
Local Signalling	White/red flag
Signalling Circuit Voltage	AC: 250 V 50/60 Hz
Signalling Output Current	0.25 A
Mounting Mode	Clip-on
Mounting Support	DIN rail
9 Mm Pitches	6
Height	81 mm
Width	54 mm
Depth	69 mm
Net Weight	400 g

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Colour	White (RAL 9003)
Response Time	<= 25 ns
Connections - Terminals	Tunnel type terminal 2.5...25 mm² rigid Tunnel type terminal 2.5...16 mm² flexible Tunnel type terminal 2.5...16 mm² flexible with ferrule
Wire Stripping Length	14 mm
Tightening Torque	3.5 N.m

Environment

Standards	UTE C 61740-51 EN 50539-11
Product Certifications	CE
Ip Degree Of Protection	IP40 on front face: IP20 on terminal:
Ik Degree Of Protection	IK03
Relative Humidity	5...90 %
Operating Altitude	2000 m
Ambient Air Temperature For Operation	-25...60 °C
Ambient Air Temperature For Storage	-40...85 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7.2 cm
Package 1 Width	6.1 cm
Package 1 Length	8.6 cm
Package 1 Weight	0.356 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Eu Rohs Directive	Not applicable, out of EU RoHS legal scope
-------------------	--
