

Product data sheet

Specifications



Acti9 - iSR remote signal auxiliary Surge Arrester

A9L16619

Main

Range Of Product	Acti9
Product Or Component Type	Remote indication auxiliary
Device Short Name	iSR
Signal Contacts Composition	1 C/O
[In] Rated Current	AC-12 3 A at 380...415 V, AC 50/60 Hz AC-12 6 A at 220...240 V, AC 50/60 Hz DC-12 1 A at 130 V, DC DC-12 1.5 A at 60 V, DC DC-12 2 A at 48 V, DC DC-12 6 A at 24 V, DC
9 Mm Pitches	1

Complementary

Mounting Mode	Fixed
Mounting Support	DIN rail
Height	84 mm
Width	9 mm
Depth	69 mm
Colour	White
Connections - Terminals	Clamp terminal (bottom) 3 cable(s) 0.16 mm ² - rigid Clamp terminal (bottom) 6 cable(s) 0.16 mm ² - flexible Clamp terminal (bottom) 1 cable(s) 0.16 mm ² - flexible with ferrule
Wire Stripping Length	9 mm
Tightening Torque	1 N.m 1.2 N.m

Environment

Standards	EN/IEC 60947-5-1
Ip Degree Of Protection	IP20 conforming to EN/IEC 60947-5-1
Tropicalisation	2 conforming to EN/IEC 60947-5-1
Relative Humidity	95 % at 55 °C
Ambient Air Temperature For Operation	-25...50 °C
Ambient Air Temperature For Storage	-40...85 °C

Packing Units

Unit Type Of Package 1	PCE
------------------------	-----

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Number Of Units In Package 1	1
Package 1 Height	2 cm
Package 1 Width	8 cm
Package 1 Length	9.5 cm
Package 1 Weight	37 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	12
Package 2 Height	5.3 cm
Package 2 Width	10 cm
Package 2 Length	26.6 cm
Package 2 Weight	504 g
Unit Type Of Package 3	S03
Number Of Units In Package 3	108
Package 3 Height	30 cm
Package 3 Width	30 cm
Package 3 Length	40 cm
Package 3 Weight	5.034 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability



Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

Well-being performance

 Reach Free Of Svhc	
 Rohs Exemption Information	Yes
Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins