



### Main

Range of product	Acti 9
Product name	Acti 9 iPRD
Product or component type	Surge arrester with pluggable cartridge
Device short name	IPRD40r
Device application	Distribution
Poles description	1P
Remote signalling	With
Signal contacts composition	1 SD (1 C/O)
Surge arrester type	Electrical distribution network
Earthing system	TN-C TT

### Complementary

Surge arrester class type	Type 2
Surge arrester technology	MOV
[Ue] rated operational voltage	230 V (+/- 10 %) AC 50/60 Hz 400 V (+/- 10 %) AC 50/60 Hz
[In] nominal discharge current	Common mode : 15 kA L/PE Common mode : 15 kA N/PE
[Imax] maximum discharge current	Common mode : 40 kA L/PE
[Uc] maximum continuous operating voltage	Common mode : 350 V L/PE Common mode : 350 V N/PE
[Up] voltage protection level	<= 1.4 kV type 2 common mode L/PE
[Ut] temporary overvoltage	Withstand : 337 V L/N for 5 s Safe failure mode : 1200 V N/PE for 200 ms
Disconnecter device type	Associated circuit breaker iC60H 50 A curve C - Icu 15 kA Associated circuit breaker iC60N 40 A curve C - Icu 10 kA Associated circuit breaker NG125H 63 A curve C - Icu 36 kA Associated circuit breaker NG125L 63 A curve C - Icu 50 kA Associated circuit breaker NG125N 40 A curve C - Icu 25 kA

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

[Isc] short-circuit current rating	50 kA
Signalling circuit voltage	0.25 A/250 V AC 50/60 Hz
Mounting mode	Clip-on
Mounting support	DIN rail
9 mm pitches	2
Height	85 mm
Width	18 mm
Depth	69 mm
Product weight	0.112 kg
Colour	White ( RAL 9003 )
Response time	<= 25 ns
[Ipe] Ground residual current	0.6 mA 0.003 mA
Connections - terminals	Tunnel type terminal, downside 2.5...35 mm <sup>2</sup> Tunnel type terminal, upside 2.5...35 mm <sup>2</sup>
Tightening torque	2.5 N.m

## Environment

Standards	EN 61643-11 : 2012 IEC 61643-11 : 2011
Product certifications	CE
Quality labels	NF KEMA-KEUR
IP degree of protection	On front face : IP40 conforming to IEC 60529 Built-in : IP20 conforming to IEC 60529
IK degree of protection	IK03 conforming to IEC 62262
Relative humidity	5...95 %
Operating altitude	2000 m
Ambient air temperature for operation	-25...60 °C
Ambient air temperature for storage	-40...85 °C

## Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0844 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available <a href="#">Product Environmental Profile</a>
Product end of life instructions	Available <a href="#">End of Life Information</a>

## Contractual warranty

Warranty period	18 months
-----------------	-----------