



Main

Range of product	Acti 9
Product name	Acti 9 iPRD
Product or component type	Surge arrester with pluggable cartridge
Device short name	IPRD40r
Device application	Distribution
Poles description	3P + N
Remote signalling	With
Signal contacts composition	1 SD (1 C/O)
Surge arrester type	Electrical distribution network
Earthing system	TT TN-S

Complementary

Surge arrester class type	Type 2
Surge arrester technology	MOV + GDT
[Ue] rated operational voltage	400 V (+/- 10 %) AC 50/60 Hz 230 V (+/- 1.5 dB) AC 50/60 Hz
[In] nominal discharge current	Common mode : 15 kA L/PE Common mode : 15 kA N/PE Differential mode : 15 kA L/N
[Imax] maximum discharge current	Common mode : 40 kA L/PE Common mode : 40 kA N/PE Differential mode : 40 kA L/N
[Uc] maximum continuous operating voltage	Common mode : 260 V N/PE Common mode : 350 V L/PE Differential mode : 350 V L/N
[Up] voltage protection level	<= 1.4 kV type 2 common mode N/PE <= 1.4 kV type 2 differential mode L/N
[Ut] temporary overvoltage	Withstand : 337 V L/N for 5 s Withstand : 442 V L/PE for 5 s Safe failure mode : 1200 V N/PE for 200 ms

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Safe failure mode : 1453 V L/PE for 200 ms

Disconnecter device type	Associated circuit breaker iC60H 50 A curve C - Icu 15 kA Associated circuit breaker iC60N 40 A curve C - Icu 10 kA Associated circuit breaker NG125H 63 A curve C - Icu 36 kA Associated circuit breaker NG125L 63 A curve C - Icu 50 kA Associated circuit breaker NG125N 40 A curve C - Icu 25 kA
[IscCR] short-circuit current rating	50 kA
Signalling circuit voltage	0.25 A/250 V AC 50/60 Hz
Mounting mode	Clip-on
Mounting support	DIN rail
9 mm pitches	8
Height	85 mm
Width	72 mm
Depth	69 mm
Product weight	0.421 kg
Colour	White (RAL 9003)
Response time	<= 25 ns
[Ipe] Ground residual current	0.003 mA 0.6 mA
Connections - terminals	Tunnel type terminal, downside 2.5...35 mm ² Tunnel type terminal, upside 2.5...35 mm ²
Tightening torque	2.5 N.m

Environment

Standards	EN 61643-11 : 2012 IEC 61643-11 : 2011
Product certifications	CE
Quality labels	KEMA-KEUR NF
IP degree of protection	On front face : IP40 conforming to IEC 60529 Built-in : IP20 conforming to IEC 60529
IK degree of protection	IK03 conforming to IEC 62262
Relative humidity	5...95 %
Operating altitude	2000 m
Ambient air temperature for operation	-25...60 °C
Ambient air temperature for storage	-40...85 °C

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0844 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available Product Environmental Profile
Product end of life instructions	Available End of Life Information

Contractual warranty

Warranty period	18 months
-----------------	-----------