



Main

Range of product	Altivar 1200
Product or component type	Medium voltage variable speed drive
Device short name	ATV1200
Product destination	Synchronous motors Asynchronous motors
Product specific application	Fan, pump, compressor, conveyor
Assembly style	In floor-standing enclosure with separate air flows

Complementary

Product composition	2 x plinth Phase-shifting transformer Medium voltage arrestors Cooling fans Human machine interface 15 x power cells
EMC filter	Integrated
Network number of phases	3 phases
Input type	30 pulse diode rectifier bridge
[Us] rated supply voltage	6 kV +/- 10 %
Supply voltage limits	2970...3630 V
[Uc] control circuit voltage	220 V
Motor power kW	393 kW
Line current	65 A
Drive efficiency with transformer (including fan power)	96 % (standard efficiency) 96.5 % (high efficiency)
Total losses at 100 % load including fan power	16 kW (standard efficiency) 14 kW (high efficiency)
Apparent power	470 kVA
Prospective line I _{sc}	31.5 kA for 150 ms
Overload withstand	1.2 I _n , standard overload, 60 s 1.5 I _n , standard overload, 3 s 1.5 I _n , high overload, 60 s 1.85 I _n , high overload, 3 s
Continuous output current	45 A (standard overload) 36 A (high overload)

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Maximum transient current	54 A for 60 s
Speed drive output frequency	0.5...120 Hz voltage/frequency ratio (V/f) 0.5...70 Hz vector control with/without speed feedback
Nominal switching frequency	600 Hz
Speed range	20...100
Asynchronous motor control profile	Vector control with sensor, optional Voltage/frequency ratio (V/f) Closed-loop control with encoder Sensorless flux vector control
Synchronous motor control profile	Closed-loop control with encoder Voltage/frequency ratio (V/f)
Overvoltage category	II conforming to EN/IEC 61800-5-1
Output voltage	<= power supply voltage
Isolation	Electrical between power and control
Electrical connection	Bar - screw type M10, clamping capacity: 6 x 40 mm ² (L1/R, L2/S, L3/T) entry from the bottom or from the top
Supply	External supply for control at 220 V AC, 3 kVA Internal supply for cooling fan at 380 V AC External supply for control at 220 V AC/DC (optional) External supply for cooling fan at 380 V AC (optional)
Analogue input number	4
Analogue input type	software-configurable current: 0...20 mA/4...20 mA, 24 V max, impedance: 250 Ohm
Analogue output number	2 4 (optional)
Analogue output type	software-configurable current: 0...20 mA/4...20 mA DC, impedance: 250 Ohm
Discrete output number	10 14 (optional)
Discrete input number	6 10 (optional)
Acceleration and deceleration ramps	Linear from 0...3200 s
Protection type	Ground fault protection: drive
Dielectric strength	20 kV AC between earth and power terminals
Communication port protocol	Human machine interface: Modbus with 2-wire RS485(1) - SUB-D 9 Human machine interface: Modbus TCP with (1) - RJ45 Human machine interface: Ethernet/IP with (1) - RJ45 Human machine interface: Profibus with (1) - SUB-D 9 Human machine interface: DeviceNet with (1) - SUB-D 9
Operating position	Vertical +/- 10 degree
Colour of enclosure	Grey (RAL 7032)
Width	2860 mm (standard efficiency) 3160 mm (high efficiency)
Depth	1400 mm (standard efficiency) 1500 mm (high efficiency)
Height	2590 mm standard efficiency 2740 mm high efficiency
Net weight	3800 kg (high efficiency) 2900 kg (standard efficiency)


Environment

IP degree of protection	IP41 IP42 IP31
Standards	EN/IEC 60204-11 EN/IEC 60529 EN/IEC 61800-3 EN/IEC 61800-4 EN/IEC 61800-5-1 IEEE 519:1992
Marking	CE
Pollution degree	2 conforming to EN/IEC 61800-5-1
Noise level	80 dB


Vibration resistance	4.9 m/s ² (f= 10...50 Hz)
Relative humidity	0...90 % 0...95 % optional
Ambient air temperature for operation	0...40 °C 40...50 °C (with current derating of 2 % per °C)
Ambient air temperature for storage	-10...60 °C
Volume of cooling air	16600 m ³ /h (standard efficiency) 19900 m ³ /h (high efficiency)
Type of cooling	Forced convection
Operating altitude	<= 1000 m without 1000...2000 m with current derating 0.6 % per 100 m

Dimensions


Standard Efficiency



High Efficiency




Clearance



Connections and Schema


Standard Wiring Diagram



- (1) Integrated power supply
- (2) Control power supply
- (3) 4-20mA speed setpoint
- (4) Input reserved
- (5) VFD is ready
- (6) Local 1 remote control
- (7) VFD running
- (8) Alarming
- (9) Detected fault
- (10) 4-20mA Output current
- (11) 4-20mA Output speed
- (12) Stop
- (13) Start
- (14) Main circuit breaker enable to close
- (15) Trip main circuit breaker
- (16) Undervoltage release module of circuit breaker
- (17) 4-20mA reserved inputs
- (18) Reserved outputs
- (QF1) Main circuit breaker


Power Derating of Output Current

Temperature Derating



(x) Ambient temperature
(y) Derating

Altitude Derating



(x) Altitude
(y) Derating