



Main

Range	Prodis
Product or component type	Add-on residual current devices
Device short name	Vigi TG40
Poles description	1P + N
Neutral position	Left
[In] rated current	40 A
Network type	AC
Earth-leakage sensitivity	300 mA
Earth-leakage protection time delay	Selective
Earth-leakage protection class	Type A-SI

Complementary

Device location in system	Group incomer
Network frequency	50 Hz
[Ue] rated operational voltage	230 V AC 50 Hz phase to neutral
Residual current tripping technology	Voltage independent
[Ui] rated insulation voltage	400 V AC 50 Hz conforming to EN 61009-1
[Uimp] rated impulse withstand voltage	6 kV conforming to EN 61009-1
Local signalling	ON/OFF indication
Mounting mode	Clip-on
Mounting support	DIN rail
Electrical connection to mcb	By screws
9 mm pitches	2
Height	82 mm
Width	18 mm
Depth	70 mm
Net weight	90 g

Colour	White
Connections - terminals	Cable upstream0.75...16 mm ² rigid Cable upstream0.33...10 mm ² flexible
Wire stripping length	13 mm
Tightening torque	2 N.m

Environment

Standards	IEC 60947-2 EN 61009-1 EN 61009-2-1
IP degree of protection	IP20 conforming to IEC 60529
Pollution degree	3 conforming to EN 61009-1
Tropicalisation	2 conforming to IEC 60068-1
Relative humidity	95 % at 55 °C
Operating altitude	2000 m
Ambient air temperature for operation	-25...60 °C
Ambient air temperature for storage	-40...60 °C

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Under investigation
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
----------	-----------