

# Product data sheet

Specifications



## variable speed drive ATV31 - 1p - 0.55kW - 1x230V - IP55 - complete

ATV31C055M2ZH28

 **Discontinued on:** Apr 19, 2021

 **Discontinued**

### Main

|                                    |                                                                                                    |
|------------------------------------|----------------------------------------------------------------------------------------------------|
| Range Of Product                   | Altivar 31                                                                                         |
| Product Or Component Type          | Variable speed drive                                                                               |
| Product Destination                | Asynchronous motors                                                                                |
| Product Specific Application       | Wire guiding<br>Simple machine                                                                     |
| Assembly Style                     | Enclosed                                                                                           |
| Component Name                     | ATV31                                                                                              |
| Emc Filter                         | Integrated                                                                                         |
| Power Supply Voltage               | 200...240 V - 15...10 %                                                                            |
| Power Supply Frequency             | 50...60 Hz - 5...5 %                                                                               |
| Network Number Of Phases           | Single phase                                                                                       |
| Motor Power Kw                     | 0.55 kW                                                                                            |
| Motor Power Hp                     | 0.75 hp                                                                                            |
| Line Current                       | 5.8 A 240 V 1 kA<br>6.8 A 200 V 1 kA                                                               |
| Apparent Power                     | 1.4 kVA                                                                                            |
| Maximum Prospective Line Isc       | 1 kA                                                                                               |
| Nominal Output Current             | 3.7 A 4 kHz                                                                                        |
| Maximum Transient Current          | 5.6 A for 60 s                                                                                     |
| Power Dissipation In W             | 46 W at nominal load                                                                               |
| Speed Range                        | 1...50                                                                                             |
| Transient Overtorque               | 150...170 % of nominal motor torque                                                                |
| Asynchronous Motor Control Profile | Factory set : constant torque<br>Sensorless flux vector control with PWM type motor control signal |
| Analogue Input Number              | 3                                                                                                  |
| Ip Degree Of Protection            | IP55                                                                                               |

### Complementary

|                               |              |
|-------------------------------|--------------|
| Power Supply Voltage Limit    | 170...264 V  |
| Power Supply Frequency Limits | 47.5...63 Hz |
| Speed Drive Output Frequency  | 0.5...500 Hz |
| Nominal Switching Frequency   | 4 kHz        |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

|                                     |                                                                                                                                                                                                                                                                                                                                                                                         |
|-------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Switching Frequency                 | 2...16 kHz adjustable                                                                                                                                                                                                                                                                                                                                                                   |
| Braking Torque                      | <= 150 % during 60 s with braking resistor<br>100 % with braking resistor continuously<br>100 % without braking resistor                                                                                                                                                                                                                                                                |
| Regulation Loop                     | Frequency PI regulator                                                                                                                                                                                                                                                                                                                                                                  |
| Motor Slip Compensation             | Automatic whatever the load<br>Adjustable<br>Suppressable                                                                                                                                                                                                                                                                                                                               |
| Output Voltage                      | <= power supply voltage                                                                                                                                                                                                                                                                                                                                                                 |
| Electrical Connection               | AI1, AI2, AI3, AOV, AOC, R1A, R1B, R1C, R2A, R2B, LI1...LI6 terminal 2.5 mm²<br>AWG 14<br>L1, L2, L3, U, V, W, PA, PB, PA/+, PC/- terminal 2.5 mm² AWG 14                                                                                                                                                                                                                               |
| Tightening Torque                   | AI1, AI2, AI3, AOV, AOC, R1A, R1B, R1C, R2A, R2B, LI1...LI6: 0.6 N.m<br>L1, L2, L3, U, V, W, PA, PB, PA/+, PC/-: 0.8 N.m                                                                                                                                                                                                                                                                |
| Insulation                          | Electrical between power and control                                                                                                                                                                                                                                                                                                                                                    |
| Supply                              | Internal supply for logic inputs 19...30 V, <100 mA overload protection<br>Internal supply for logic inputs 19...30 V, <100 mA short-circuit protection<br>Internal supply for reference potentiometer 10...10.8 V, <10 mA overload protection<br>Internal supply for reference potentiometer 10...10.8 V, <10 mA short-circuit protection                                              |
| Analogue Input Type                 | AI3 configurable current 0...20 mA, impedance: 250 Ohm<br>AI1 configurable voltage 0...10 V, input voltage 30 V max, impedance: 30000 Ohm<br>AI2 configurable voltage +/- 10 V, input voltage 30 V max, impedance: 30000 Ohm                                                                                                                                                            |
| Input Sampling Time                 | LI1...LI6: 4 ms discrete<br>AI1, AI2, AI3: 8 ms analog                                                                                                                                                                                                                                                                                                                                  |
| Output Response Time                | AOV, AOC 8 ms for analog<br>R1A, R1B, R1C, R2A, R2B 8 ms for discrete                                                                                                                                                                                                                                                                                                                   |
| Linearity Error                     | +/- 0.2 % for output                                                                                                                                                                                                                                                                                                                                                                    |
| Analogue Output Number              | 2                                                                                                                                                                                                                                                                                                                                                                                       |
| Analogue Output Type                | AOC configurable current: 0...20 mA, impedance: 800 Ohm, resolution: 8 bits<br>AOV configurable voltage: 0...10 V, impedance: 470 Ohm, resolution: 8 bits                                                                                                                                                                                                                               |
| Discrete Input Logic                | Positive logic (source) (LI1...LI6), < 5 V (state 0), > 11 V (state 1)<br>Logic input not wired (LI1...LI4), < 13 V (state 1)<br>Negative logic (source) (LI1...LI6), > 19 V (state 0)                                                                                                                                                                                                  |
| Discrete Output Number              | 2                                                                                                                                                                                                                                                                                                                                                                                       |
| Discrete Output Type                | Configurable relay logic: (R1A, R1B, R1C) 1 NO + 1 NC - 100000 cycles<br>Configurable relay logic: (R2A, R2B) NC - 100000 cycles                                                                                                                                                                                                                                                        |
| Minimum Switching Current           | 10 mA 5 V DC R1-R2                                                                                                                                                                                                                                                                                                                                                                      |
| Maximum Switching Current           | 2 A at 250 V AC on inductive load - cos phi = 0.4 - L/R = 7 ms (R1-R2)<br>2 A at 30 V DC on inductive load - cos phi = 0.4 - L/R = 7 ms (R1-R2)<br>5 A at 250 V AC on resistive load - cos phi = 1 - L/R = 0 ms (R1-R2)<br>5 A at 30 V DC on resistive load - cos phi = 1 - L/R = 0 ms (R1-R2)                                                                                          |
| Discrete Input Number               | 6                                                                                                                                                                                                                                                                                                                                                                                       |
| Discrete Input Type                 | (LI1...LI6) programmable at 24 V, 0...100 mA for PLC, impedance: 3500 Ohm                                                                                                                                                                                                                                                                                                               |
| Acceleration And Deceleration Ramps | Linear adjustable separately from 0.1 to 999.9 s<br>S, U or customized                                                                                                                                                                                                                                                                                                                  |
| Braking To Standstill               | By DC injection                                                                                                                                                                                                                                                                                                                                                                         |
| Protection Type                     | Input phase breaks: drive<br>Line supply overvoltage and undervoltage safety circuits: drive<br>Line supply phase loss safety function, for three phases supply: drive<br>Motor phase breaks: drive<br>Overcurrent between output phases and earth (on power up only): drive<br>Overheating protection: drive<br>Short-circuit between motor phases: drive<br>Thermal protection: motor |

|                             |                                                                                                                    |
|-----------------------------|--------------------------------------------------------------------------------------------------------------------|
| Insulation Resistance       | >= 500 mOhm 500 V DC for 1 minute                                                                                  |
| Local Signalling            | 1 LED (red) for drive voltage<br>Four 7-segment display units for CANopen bus status                               |
| Time Constant               | 5 ms for reference change                                                                                          |
| Frequency Resolution        | Display unit: 0.1 Hz<br>Analog input: 0.1...100 Hz                                                                 |
| Communication Port Protocol | CANopen<br>Modbus                                                                                                  |
| Connector Type              | 1 RJ45 for CANopen via VW3 CANTAP2 adaptor<br>1 RJ45 for Modbus                                                    |
| Physical Interface          | RS485 multidrop serial link for Modbus                                                                             |
| Transmission Frame          | RTU for Modbus                                                                                                     |
| Transmission Rate           | 10, 20, 50, 125, 250, 500 kbps or 1 Mbps for CANopen via VW3 CANTAP2 adaptor<br>4800, 9600 or 19200 bps for Modbus |
| Number Of Addresses         | 1...127 for CANopen via VW3 CANTAP2 adaptor<br>1...247 for Modbus                                                  |
| Number Of Drive             | 127 for CANopen via VW3 CANTAP2 adaptor<br>31 for Modbus                                                           |
| Marking                     | CE                                                                                                                 |
| Operating Position          | Vertical +/- 10 degree                                                                                             |
| Net Weight                  | 6.3 kg                                                                                                             |

## Environment

|                                       |                                                                                                                                                                                                                                                                                                                                                   |
|---------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Dielectric Strength                   | 2040 V DC between earth and power terminals<br>2880 V AC between control and power terminals                                                                                                                                                                                                                                                      |
| Electromagnetic Compatibility         | 1.2/50 µs - 8/20 µs surge immunity test level 3 conforming to IEC 61000-4-5<br>Electrical fast transient/burst immunity test level 4 conforming to IEC 61000-4-4<br>Electrostatic discharge immunity test level 3 conforming to IEC 61000-4-2<br>Radiated radio-frequency electromagnetic field immunity test level 3 conforming to IEC 61000-4-3 |
| Standards                             | EN 50178                                                                                                                                                                                                                                                                                                                                          |
| Product Certifications                | C-Tick<br>CSA<br>UL<br>N998                                                                                                                                                                                                                                                                                                                       |
| Pollution Degree                      | 2                                                                                                                                                                                                                                                                                                                                                 |
| Protective Treatment                  | TC                                                                                                                                                                                                                                                                                                                                                |
| Vibration Resistance                  | 1 gn (f= 13...150 Hz) conforming to EN/IEC 60068-2-6<br>1.5 mm (f= 3...13 Hz) conforming to EN/IEC 60068-2-6                                                                                                                                                                                                                                      |
| Shock Resistance                      | 15 gn for 11 ms conforming to EN/IEC 60068-2-27                                                                                                                                                                                                                                                                                                   |
| Relative Humidity                     | 5...95 % without condensation conforming to IEC 60068-2-3<br>5...95 % without dripping water conforming to IEC 60068-2-3                                                                                                                                                                                                                          |
| Ambient Air Temperature For Storage   | -25...70 °C                                                                                                                                                                                                                                                                                                                                       |
| Ambient Air Temperature For Operation | -10...50 °C without derating (with protective cover on top of the drive)<br>-10...60 °C with derating factor (without protective cover on top of the drive)                                                                                                                                                                                       |
| Operating Altitude                    | <= 1000 m without derating<br>>= 1000 m with current derating 1 % per 100 m                                                                                                                                                                                                                                                                       |