

# Product data sheet

Specifications



## switch Acti9 iSW with indicator - 1 pole - 32 A - 250V

A9S61132

### Main

Range	Acti9
Product Name	Acti9 iSW
Product Or Component Type	Switch disconnecter
Device Short Name	iSW
Device Application	Control
Poles Description	1P
Utilisation Category	AC-22A

### Complementary

[Ie] Rated Operational Current	32 A at 250 V AC 50/60 Hz
[Ue] Rated Operational Voltage	250 V AC 50/60 Hz
[Ui] Rated Insulation Voltage	250 V AC 50/60 Hz conforming to IEC EN 60669-1
[Uimp] Rated Impulse Withstand Voltage	4 kV
Control Type	Toggle
Local Signalling	ON/OFF indication and lamp
Signalling Circuit Voltage	AC: 230 V 50/60 Hz
Mounting Mode	Fixed
Mounting Support	DIN rail
9 Mm Pitches	2
Height	77 mm
Width	18 mm
Depth	70 mm
Colour	White
Mechanical Durability	300000 cycles
Electrical Durability	30000 cycles
Connections - Terminals	Tunnel type terminals - 10 mm² - rigid Tunnel type terminals - 10 mm² - flexible Tunnel type terminals - 10 mm² - flexible with ferrule
Wire Stripping Length	9 mm
Tightening Torque	1.2 N.m

### Environment

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Standards	IEC EN 60669-1
Ip Degree Of Protection	IP4
Pollution Degree	2
Tropicalisation	2
Relative Humidity	95 % at 55 °C
Ambient Air Temperature For Operation	-20...50 °C
Ambient Air Temperature For Storage	-40...70 °C

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.0 cm
Package 1 Width	6.5 cm
Package 1 Length	8.0 cm
Package 1 Weight	60.0 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	12
Package 2 Height	8.0 cm
Package 2 Width	9.5 cm
Package 2 Length	23.0 cm
Package 2 Weight	775.0 g
Unit Type Of Package 3	S03
Number Of Units In Package 3	144
Package 3 Height	30.0 cm
Package 3 Width	30.0 cm
Package 3 Length	40.0 cm
Package 3 Weight	9.787 kg

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information   Yes

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	<a href="#">End of Life Information</a>