



Main

Range	Acti 9
Product name	Acti 9 iID
Product or component type	Residual current circuit breaker (RCCB)
Device short name	iID
Poles description	4P
Neutral position	Left
[In] rated current	100 A
Network type	AC
Earth-leakage sensitivity	30 mA
Earth-leakage protection time delay	Instantaneous
Earth-leakage protection class	Type A

Complementary

Network frequency	50/60 Hz
[Ue] rated operational voltage	380...415 V AC 50/60 Hz
Rated breaking and making capacity	I _m 1500 A I _{dm} 1500 A
Rated conditional short-circuit current	10 kA
[Ui] rated insulation voltage	500 V AC 50/60 Hz
[Uimp] rated impulse withstand voltage	6 kV
Contact position indicator	Yes
Control type	Toggle
Mounting mode	Clip-on
Mounting support	DIN rail
9 mm pitches	8
Height	91 mm
Width	72 mm
Depth	73 mm
Product weight	0.37 kg

Colour	White
Mechanical durability	20000 cycles
Electrical durability	10000 cycles AC-1
Locking options description	Padlocking device
Connections - terminals	Double terminal, front rigid wire(s) 1...35 mm ² max Double terminal, front flexible wire(s) 1...25 mm ² max Double terminal, front flexible with ferrule wire(s) 1...25 mm ² max Double terminal, back rigid wire(s) 1...25 mm ² max Double terminal, back flexible wire(s) 1...16 mm ² max Double terminal, back flexible with ferrule wire(s) 1...16 mm ² max
Wire stripping length	14 mm (top or bottom)
Tightening torque	3.5 N.m (top or bottom)

Environment

Standards	EN/IEC 61008-1
IP degree of protection	IP40 for modular enclosure conforming to IEC 60529 IP20 conforming to IEC 60529
Pollution degree	3
Electromagnetic compatibility	8/20 µs impulse withstand, 250 A conforming to EN/IEC 61008-1
Ambient air temperature for operation	-25...60 °C
Ambient air temperature for storage	-40...85 °C

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0627 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available Product Environmental Profile
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------