

Product data sheet

Specifications



output interface module - 17.5 mm - electromechanical - 48 V AC/DC - 1 NO

ABR1S118E

Discontinued on: Oct 1, 2021

Discontinued

Main

Range Of Product	Interface for discrete signals
Product Or Component Type	Electromechanical output interface module
Contacts Type And Composition	1 NO
[Uc] Control Circuit Voltage	48 V
Control Circuit Type	AC/DC
Control Circuit Frequency	50/60 Hz
Width Pitch Dimension	17.5 mm
Maximum [In] Rated Current	32 mA AC 36 mA DC
Reverse Polarity Protection	With
Short-Circuit Protection	16 A external fuse gF (Ik <= 2.5 kA AC and Ik <= 100 A DC) 16 A external fuse gG (Ik <= 2.5 kA AC and Ik <= 100 A DC)
[Ith] Conventional Free Air Thermal Current	12 A conforming to IEC 60947-1
Local Signalling	Green mechanical indicator for position of contacts and 1 green LED control signal state

Complementary

Control Circuit Voltage Limits	53 V energization threshold: 34 V
Maximum Switching Voltage	125 V DC
Housing Colour	Grey
Connections - Terminals	Screw clamp terminal
Drop-Out Voltage	8.5 V
Minimum Holding Current	4.7 mA DC 5.4 mA AC
Maximum Power Dissipation In W	1.5 W
[Ue] Rated Operational Voltage	<= 125 V DC conforming to IEC 60947-5-1 <= 230 V AC conforming to IEC 60947-5-1
Network Frequency	50/60 Hz
[Ie] Rated Operational Current	1 A AC-13 Ue: 230 V per 1000000 cycles conforming to IEC 60947-5-1 1 A AC-14 Ue: 230 V per 1000000 cycles conforming to IEC 60947-5-1 1 A AC-15 Ue: 230 V per 1000000 cycles conforming to IEC 60947-5-1 1 A DC-13 Ue: 24 V per 1000000 cycles conforming to IEC 60947-5-1 4 A AC-12 Ue: 230 V per 1000000 cycles conforming to IEC 60947-5-1 5 A DC-12 Ue: 24 V per 1000000 cycles conforming to IEC 60947-5-1
Minimum Switching Current	3 mA

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Minimum Switching Voltage	17 V
Electrical Reliability	<= 0.00000001
Operating Time	<= 12 ms between de-energisation of coil and closing of NC contact <= 12 ms between de-energisation of coil and closing of NO contact <= 12 ms between energisation of coil and closing of NC contact <= 12 ms between energisation of coil and closing of NO contact
Contact Bounce Time	<= 3 ms
Operating Rate In Hz	6 Hz at no-load 0.5 Hz at Ie
Mechanical Durability	20000000 cycles
[Ui] Rated Insulation Voltage	250 V conforming to IEC 60947-1 250 V conforming to VDE 0110 group C
Flame Retardance	V0 conforming to UL 94
Cable Cross Section	0.34...2.5 mm², 1 or 2 wires flexible with cable end 0.6...2.5 mm², 1 or 2 wires flexible without cable end 0.27...2.5 mm², 2 wires rigid 0.27...4 mm², 1 wire rigid
Operating Position	Any position
Installation Category	II conforming to IEC 60947-1
Mounting Support	Combination rail Asymmetrical DIN rail Symmetrical DIN rail
Net Weight	0.095 kg

Environment

Immunity To Microbreaks	10 ms
Dielectric Strength	1500 V for 1 minute between independent contacts 2500 V for 1 minute between wired interface and earth 4000 V for 1 minute between coil circuit and contact circuits
Standards	IEC 60947-5-1
Product Certifications	LROS (Lloyds register of shipping) DNV UL CSA BV
Ip Degree Of Protection	IP20 conforming to IEC 60529
Protective Treatment	TC
Fire Resistance	850 °C conforming to IEC 60695-2-1
Shock Resistance	50 gn for 11 ms conforming to IEC 60068-2-27
Vibration Resistance	6 gn conforming to IEC 60068-2-6 (f = 10...55 Hz)
Electromagnetic Compatibility	1.2/50 ms shock waves immunity test conforming to IEC 255-4 Electrostatic discharge immunity test, level 3 8 kV conforming to IEC 61000-4-2 Rapid transients immunity test on input/output 1 kV conforming to IEC 61000-4-4 Rapid transients immunity test on power supply 2 kV conforming to IEC 61000-4-4
Ambient Air Temperature For Operation	-20...60 °C at Un -5...40 °C unrestricted operation
Ambient Air Temperature For Storage	-40...70 °C
Operating Altitude	<= 3000 m
Pollution Degree	3 conforming to IEC 60947-5-1

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.8 cm
Package 1 Width	7 cm
Package 1 Length	7.5 cm
Package 1 Weight	96 g

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance



Mercury Free



RoHS Exemption Information

Yes


Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Dimensions Drawings

Electromechanical Interface Module

Dimensions




Connections and Schema

Electromechanical Interface Module

Example of Application with PLC

Interfacing PLC discrete outputs




- (1) Essential on inductive loads (can be replaced with peak limiter)
- (2) PLC positive logic transistor (or relay) outputs

Interface with Mechanical Indication + LED

Circuit Diagram

1 N/O




Performance Curves

Electrical Durability of Contacts

AC Loads

Test conditions: in accordance with standard IEC 947-5-1 set up for rated control voltage, operating rate: 1800 cycles/hour. (0.5 Hz).


AC-12 operating cycles in millions



AC-12 Control of resistive loads and isolated solid state loads via optocoupler ($\cos \phi \geq 0.9$)

- (1) 24 V
- (2) 48 V
- (3) 127 V
- (4) 230 V


AC-13 operating cycles in millions



AC-13 Control of isolated solid state loads via transformer ($\cos \phi \geq 0.65$)

- (1) 24 V
- (2) 48 V
- (3) 127 V
- (4) 230 V

AC-14 and AC-15 operating cycles in millions



AC-14 Control of weak electromagnetic loads of electromagnets ≤ 72 VA (make: $\cos \phi = 0.3$, break: $\cos \phi = 0.3$)


AC-15 Control of electromagnetic loads of electromagnets > 72 VA (make: $\cos \phi = 0.7$, break: $\cos \phi = 0.4$)

- (1) 24 V
- (2) 48 V
- (3) 127 V
- (4) 230 V

DC Loads

Test conditions: in accordance with standard IEC 947-5-1 set up for rated control voltage, operating rate: 1800 cycles/hour. (0.5 Hz).


DC-12 operating cycles in millions



DC-12 Control of resistive loads and isolated solid state loads via optocoupler ($L/R \leq 1$ ms)

- (1) 24 V
- (2) 48 V
- (3) 127 V

DC-13 operating cycles in millions



DC-13 Control of electromagnets ($L/R \leq 2 \times (U_e \times I_e)$ in ms, with U_e : rated operating voltage and I_e : rated operating current)

- (1) 24 V
- (2) 48 V
- (3) 127 V