

# Product data sheet

Specifications



Cable ends, Linergy TR cable ends, single conductor, white, 0.75 mm², for insulated, medium size, 5 sets of 200

AZ5CE007D

## Main

Range Of Product	Linergy
Product Or Component Type	Cable end
Cable End Size	Medium
Standards	DIN 46228-4
Type Of Packing	Dispenser pack
Quantity Per Set	5 sets of 200
Cable Cross Section	0.75 mm²

## Complementary

Cable End Type	Single conductor
Additional Information	Without marker tag holder
Colour	Grey
Bezel Material	Halogen-free plastic
Tube Material	Copper conforming to ISO 1337
Number Of Cables	1
Awg Gauge	AWG 20
Bezel Size	Ø 3.3 mm
Tube Diameter	1.5 mm
Length	14 mm
Tube Length	8 mm
Net Weight	0.15 kg

## Environment

Product Certifications	UL
Ambient Air Temperature For Operation	-20...105 °C

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.400 cm
Package 1 Width	0.400 cm
Package 1 Length	1.400 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Weight	0.100 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	1000
Package 2 Height	13.000 cm
Package 2 Width	7.000 cm
Package 2 Length	12.600 cm
Package 2 Weight	138.000 g
Unit Type Of Package 3	S01
Number Of Units In Package 3	5000
Package 3 Height	15.000 cm
Package 3 Width	15.000 cm
Package 3 Length	40.000 cm
Package 3 Weight	914.000 g

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

✓ Pvc Free

✓ Halogen Free Plastic Parts Product

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations