

Product data sheet

Specifications



servo motor BCH, Lexium 28,
130mm, 1500W, 10kg.cm², without
oil seal, with key, brake, straight
connection

BCH2MM1521CF6C

! Discontinued

! Discontinued on: Jul 28, 2023

Main

Range Compatibility	Lexium 28
Product Or Component Type	Servo motor
Device Short Name	BCH2

Complementary

Maximum Mechanical Speed	3000 rpm
[Us] Rated Supply Voltage	220 V
Network Number Of Phases	Three phase Single phase
Continuous Stall Current	6.18 A
Continuous Stall Torque	7.16 N.m for LXM28... at 7 A, 220 V, single phase 7.16 N.m for LXM28... at 7 A, 220 V, three phase
Continuous Power	1500 W
Peak Stall Torque	21.48 N.m for LXM28... at 7 A, 220 V, single phase 21.48 N.m for LXM28... at 7 A, 220 V, three phase
Nominal Output Power	1500 W for LXM28... at 7 A, 220 V, single phase 1500 W for LXM28... at 7 A, 220 V, three phase
Nominal Torque	7.16 N.m for LXM28... at 7 A, 220 V, single phase 7.16 N.m for LXM28... at 7 A, 220 V, three phase
Nominal Speed	2000 rpm for LXM28... at 7 A, 220 V, single phase 2000 rpm for LXM28... at 7 A, 220 V, three phase
Maximum Current Irms	20.31 A for LXM28... at 1.5 kW, 220 V
Maximum Permanent Current	6.74 A
Product Compatibility	LXM28... servo drive motor at 1.5 kW, 220 V, single phase LXM28... servo drive motor at 1.5 kW, 220 V, three phase
Shaft End	Keyed
Shaft Diameter	22 mm
Shaft Length	55 mm
Key Width	8 mm
Feedback Type	20 bits single turn absolute encoder
Holding Brake	With
Holding Torque	9.6 N.m built-in
Mounting Support	Asian standard flange

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Motor Flange Size	130 mm
Electrical Connection	Connector MIL
Torque Constant	1.16 N.m/A at 20 °C
Back Emf Constant	70 V/krpm at 20 °C
Rotor Inertia	10 kg.cm²
Stator Resistance	0.64 Ohm at 20 °C
Stator Inductance	6.4 mH at 20 °C
Stator Electrical Time Constant	10 ms at 20 °C
Maximum Radial Force Fr	670 N at 2000 rpm
Maximum Axial Force Fa	200 N
Brake Pull-In Power	19.7 W
Type Of Cooling	Natural convection
Length	202 mm
Number Of Motor Stacks	3
Centring Collar Diameter	110 mm
Centring Collar Depth	8 mm
Number Of Mounting Holes	4
Mounting Holes Diameter	9.2 mm
Circle Diameter Of The Mounting Holes	145 mm
Distance Shaft Shoulder-Flange	8 mm
Net Weight	8.8 kg

Environment

Ip Degree Of Protection	IP54 IM B5, IM V1 IP50 IM V3
Ambient Air Temperature For Operation	0...40 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	18.1 cm
Package 1 Width	23.0 cm
Package 1 Length	36.0 cm
Package 1 Weight	9.84 kg

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)


Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Dimensions Drawings

Dimensions

Dimensions of Motor




	mm	in.
L (without holding brake)	167	6.57
L (with holding brake)	202	7.95
Z	114.5	4.51

Performance Curves

Torque/Speed Curves with 230 V Single/Three Phase Supply Voltage

Servo Motor with LXM28AU15 Servo Drive



- 1 : Peak torque
- 2 : Continuous torque