

Product data sheet

Specifications



medium voltage variable speed drive ATV1200 - 6.3 kV - 7200 kVA

ATV1200A78606363

Main

Range Of Product	Altivar 1200
Product Or Component Type	Medium voltage variable speed drive
Device Short Name	ATV1200
Product Destination	Asynchronous motors
Product Specific Application	Fan, pump, compressor, conveyor
Assembly Style	In floor-standing enclosure with separate air flows

Complementary

Product Composition	2 x plinth Phase-shifting transformer Medium voltage arrestors Cooling fans Human machine interface 18 x power cells
Emc Filter	Integrated
Network Number Of Phases	3 phases
Input Type	36 pulse diode rectifier bridge
[Us] Rated Supply Voltage	6.3 kV +/- 10 %
Supply Voltage Limits	2970...3630 V
[Uc] Control Circuit Voltage	220 V
Motor Power Kw	6019 kW
Line Current	720 A
Drive Efficiency With Transformer (Including Fan Power)	96 % (standard efficiency)
Total Losses At 100 % Load Including Fan Power	211 kW (standard efficiency)
Apparent Power	7200 kVA
Prospective Line Isc	31.5 kA for 150 ms
Overload Withstand	1.2 In, standard overload, 60 s 1.5 In, standard overload, 3 s 1.5 In, high overload, 60 s 1.85 In, high overload, 3 s
Continuous Output Current	660 A (standard overload) 528 A (high overload)
Maximum Transient Current	793 A for 60 s
Speed Drive Output Frequency	0.5...120 Hz voltage/frequency ratio (V/f) 0.5...70 Hz vector control with/without speed feedback
Nominal Switching Frequency	600 Hz

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Speed Range	20...100
Asynchronous Motor Control Profile	Sensorless flux vector control Closed-loop control with encoder Voltage/frequency ratio (V/f) Vector control with sensor, optional
Synchronous Motor Control Profile	Voltage/frequency ratio (V/f) Closed-loop control with encoder
Overvoltage Category	II conforming to EN/IEC 61800-5-1
Output Voltage	<= power supply voltage
Isolation	Electrical between power and control
Electrical Connection	Bar - screw type M10, clamping capacity: 6 x 40 mm² (L1/R, L2/S, L3/T) entry from the bottom or from the top
Supply	External supply for control at 220 V AC, 3 kVA Internal supply for cooling fan at 380 V AC External supply for control at 220 V AC/DC (optional) External supply for cooling fan at 380 V AC (optional)
Analogue Input Number	4
Analogue Input Type	software-configurable current: 0...20 mA/4...20 mA, 24 V max, impedance: 250 Ohm
Analogue Output Number	2 4 (optional)
Analogue Output Type	software-configurable current: 0...20 mA/4...20 mA DC, impedance: 250 Ohm
Discrete Output Number	10 14 (optional)
Discrete Input Number	6 10 (optional)
Acceleration And Deceleration Ramps	Linear from 0...3200 s
Protection Type	Ground fault protection: drive
Dielectric Strength	20 kV AC between earth and power terminals
Communication Port Protocol	Human machine interface: Modbus with 2-wire RS485(1) - SUB-D 9 Human machine interface: Modbus TCP with (1) - RJ45 Human machine interface: EtherNet/IP with (1) - RJ45 Human machine interface: Profibus with (1) - SUB-D 9 Human machine interface: DeviceNet with (1) - SUB-D 9
Operating Position	Vertical +/- 10 degree
Colour Of Enclosure	Grey (RAL 7032)
Width	9770 mm (standard efficiency)
Depth	1700 mm (standard efficiency)
Height	3040 mm standard efficiency
Net Weight	20800 kg (standard efficiency)

Environment


Ip Degree Of Protection	IP42 IP31 IP41
Standards	EN/IEC 60204-11 EN/IEC 60529 EN/IEC 61800-3 EN/IEC 61800-4 EN/IEC 61800-5-1
Marking	CE
Pollution Degree	2 conforming to EN/IEC 61800-5-1

Noise Level	80 dB
Vibration Resistance	4.9 m/s² (f= 10...50 Hz)
Relative Humidity	0...90 % 0...95 % optional
Ambient Air Temperature For Operation	0...40 °C 40...50 °C (with current derating of 2 % per °C)
Ambient Air Temperature For Storage	-10...60 °C
Volume Of Cooling Air	100000 m3/h (standard efficiency)
Type Of Cooling	Forced convection
Operating Altitude	<= 1000 m without derating 1000...2000 m with current derating 0.6 % per 100 m

Dimensions Drawings


Dimensions

Standard Efficiency



Mounting and Clearance


Clearance



Connections and Schema

Connections and Schema

Standard Wiring Diagram




- (1) Integrated power supply
- (2) Control power supply
- (3) 4-20mA speed setpoint
- (4) Input reserved
- (5) VFD is ready
- (6) Local 1 remote control
- (7) VFD running
- (8) Alarming
- (9) Detected fault
- (10) 4-20mA Output current
- (11) 4-20mA Output speed
- (12) Stop
- (13) Start
- (14) Main circuit breaker enable to close
- (15) Trip main circuit breaker
- (16) Undervoltage release module of circuit breaker
- (17) 4-20mA reserved inputs
- (18) Reserved outputs
- (QF1) Main circuit breaker

Performance Curves


Power Derating of Output Current

Temperature Derating



- (x) Ambient temperature
- (y) Derating

Altitude Derating



- (x) Altitude
- (y) Derating