

Product data sheet

Specifications



servo motor BCH, Lexium 28,
130mm, 2000W, with oil seal,
smooth, brake, straight connection

BCH2MM2022CF6C

Main

Range Compatibility	Lexium 28
Product Or Component Type	Servo motor
Device Short Name	BCH2

Complementary

Maximum Mechanical Speed	3000 rpm
[Us] Rated Supply Voltage	220 V
Network Number Of Phases	Three phase
Continuous Stall Current	9.95 A
Continuous Stall Torque	9.55 N.m for LXM28... at 12 A, 220 V, three phase
Continuous Power	2000 W
Peak Stall Torque	28.65 N.m for LXM28... at 12 A, 220 V, three phase
Nominal Output Power	2000 W for LXM28... at 12 A, 220 V, three phase
Nominal Torque	9.55 N.m for LXM28... at 12 A, 220 V, three phase
Nominal Speed	2000 rpm for LXM28... at 12 A, 220 V, three phase
Maximum Current Irms	32.85 A for LXM28... at 2 kW, 220 V
Maximum Permanent Current	11.25 A
Product Compatibility	LXM28... servo drive motor at 2 kW, 220 V, three phase
Shaft End	Smooth shaft
Shaft Diameter	22 mm
Shaft Length	55 mm
Feedback Type	20 bits single turn absolute encoder
Holding Brake	With
Holding Torque	9.6 N.m built-in
Mounting Support	Asian standard flange
Motor Flange Size	130 mm
Electrical Connection	Connector MIL
Torque Constant	0.96 N.m/A at 20 °C
Back Emf Constant	58 V/krpm at 20 °C
Rotor Inertia	14.1 kg.cm²
Stator Resistance	0.34 Ohm at 20 °C

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Stator Inductance	4.5 mH at 20 °C
Stator Electrical Time Constant	13.24 ms at 20 °C
Maximum Radial Force Fr	670 N at 2000 rpm
Maximum Axial Force Fa	200 N
Brake Pull-In Power	19.7 W
Type Of Cooling	Natural convection
Length	216 mm
Number Of Motor Stacks	4
Centring Collar Diameter	110 mm
Centring Collar Depth	8 mm
Number Of Mounting Holes	4
Mounting Holes Diameter	9.2 mm
Circle Diameter Of The Mounting Holes	145 mm
Distance Shaft Shoulder-Flange	8 mm
Net Weight	11 kg

Environment

Ip Degree Of Protection	IP50 IM V3 IP65 IM B5, IM V1
Ambient Air Temperature For Operation	0...40 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	18.1 cm
Package 1 Width	23.0 cm
Package 1 Length	36.0 cm
Package 1 Weight	10.21 kg

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)


Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Dimensions Drawings

Dimensions

Dimensions of Motor




	mm	in.
L (without holding brake)	187	7.36
L (with holding brake)	216	8.5
Z	134.5	5.30

Performance Curves

Torque/Speed Curves with 230 V Three Phase Supply Voltage

Servo Motor with LXM28AU20 Servo Drive



- 1 : Peak torque
- 2 : Continuous torque