



### Main

Range	PowerLogic
Product name	PowerLogic BCPM
Product or component type	Multi-circuit energy meter
Device short name	BCPMA
Model type	Advanced
Power monitoring	Basic instrumentation
Energy management	Sub billing and cost allocation
Device application	Sub billing
Power quality analysis	Voltage sag and swell detection
Type of measurement	Voltage Current Frequency Active power Power factor Active energy
[Us] rated supply voltage	90...277 V, AC, 50/60 Hz +/- 1 %
Network frequency	50 Hz 60 Hz

### Complementary

Current transformer input	Solid core CT, 100 A x 84
Update time	1.8 s
Measurement voltage	90...277 V phase to neutral 150...480 V phase to phase
Measurement accuracy	2 % branch current 0.25...2 A 1 % branch current 2...100 A 3 % mains current 1...100 % 3 % mains current 2...100 % 1 % voltage 90...277 V
Sampling rate	256 samples/cycle
Connection pitch	19 mm
Provided equipment	84 x current transformer 4 x cables
Communication port protocol	Modbus RTU
Communication port support	RS485

Communication of data	Over voltage alarm High current alarm Low current alarm Under voltage alarm Low-low current alarm High-high current alarm
-----------------------	--

## Environment

Mounting mode	Panel-mounted
Mounting support	Enclosure Panel
Relative humidity	95 % between 0...60 °C
Ambient air temperature for storage	-40...70 °C
Operating altitude	3000 m
Standards	ANSI C12.1 IEC 61036 EN 61010 UL 508
Product certifications	UL
Width	288 mm
Height	146 mm
Product weight	1.5 kg

## Offer Sustainability

RoHS (date code: YYWW)	Will not be compliant <a href="#">Will not be compliant</a>
------------------------	--

## Contractual warranty

Warranty period	18 months
-----------------	-----------