

Product data sheet

Specifications



BCPM power monitoring advanced + ethernet - 30 split core CT 50 A

BCPMSCE30S

⚠ To be discontinued on: Dec 31, 2024

⚠ To be end-of-service on: Dec 31, 2032

⚠ To be discontinued

Main

Range	PowerLogic
Product Name	PowerLogic BCPMSC
Product Or Component Type	Multi-circuit energy meter
Device Short Name	BCPMSCE
Model Type	Advanced + ethernet
Power Monitoring	Basic instrumentation
Energy Management	Sub billing and cost allocation
Device Application	Sub billing
Power Quality Analysis	voltage sag and swell detection
Type Of Measurement	Voltage Current Frequency Active power Power factor Active energy
[Us] Rated Supply Voltage	90...277 V AC 50/60 Hz +/- 1 %
Network Frequency	50 Hz 60 Hz

Complementary

Current Transformer Input	Split core CT 0.333 V30 x
Update Time	1.8 s
Measurement Voltage	90...277 V phase to neutral 150...480 V phase to phase
Measurement Accuracy	Branch current 2 % 0.25...2 A Branch current 1 % 2...100 A Mains current 3 % 1...100 % Mains current 3 % 2...100 % Voltage 1 % 90...277 V
Sampling Rate	256 samples/cycle
Provided Equipment	2 x cables 2 x adapter board 30 x current transformer
Communication Port Protocol	Modbus RTU BACnet IP BACnet MS/TP Modbus TCP SNMP v2

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Communication Port Support	RS485 ETHERNET
Communication Of Data	Low current alarm Over voltage alarm High current alarm Low-low current alarm High-high current alarm Under voltage alarm

Environment

Mounting Mode	Fixed
Mounting Support	Chassis
Relative Humidity	0...95 % at 0...60 °C
Ambient Air Temperature For Storage	-40...70 °C
Operating Altitude	3000 m
Standards	ANSI C12.1 UL 508 EN 61010 IEC 61036
Product Certifications	UL
Width	253 mm
Depth	71 mm
Height	307 mm
Net Weight	1.5 kg

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	14.287 cm
Package 1 Width	15.24 cm
Package 1 Length	19.05 cm
Package 1 Weight	8.21 kg

Sustainability



Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

Well-being performance

 Mercury Free	
 Rohs Exemption Information	Yes
Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
California Proposition 65	WARNING: Cancer and Reproductive Harm - www.P65Warnings.ca.gov