



### Main

Range of product	Altivar Process ATV600
Product or component type	Variable speed drive
Product specific application	Process and utilities
Device short name	ATV660
Product destination	Asynchronous motors Synchronous motors
Assembly style	In floor-standing enclosure compact version
Provided equipment	Enclosure Spacial SF Graphical operating panel in the enclosure door Frequency inverter Main switch Line choke Terminal block for main supply Terminal block for motor
Cable entry	Bottom
Colour of enclosure	Light grey RAL 7035
IP degree of protection	IP23 conforming to IEC 61800-5-1
Type of cooling	Forced convection
[Us] rated supply voltage	480 V (+/- 10 %)
Supply frequency	50/60 Hz (+/-5 %)
Network number of phases	3 phases
Overvoltage category	III
Asynchronous motor control profile	Optimized torque mode Constant torque standard Variable torque standard
Synchronous motor control profile	Permanent magnet motor
Output voltage	<= power supply voltage
Permissible temporary current boost	1.1 x In for 60 s (normal duty) 1.5 x In for 60 s (heavy duty)
Nominal switching frequency	2.5 kHz
Switching frequency	2...8 kHz adjustable with derating factor
Speed drive output frequency	0.1...500 Hz
Motor power kW	560 kW (normal duty) 450 kW (heavy duty)
Continuous output current	730 A at 2.5 kHz (heavy duty)

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

	900 A at 2.5 kHz (normal duty)
Maximum transient current	990 A during 60 s per 10 min (normal duty) 1095 A during 60 s per 10 min (heavy duty)
Line current	789 A at 480 V (normal duty) 637 A at 480 V (heavy duty)
Apparent power	656 kVA at 480 V (normal duty) 530 kVA at 480 V (heavy duty)
THDI	<= 39 % at full load conforming to IEC 61000-3-12
Short-circuit protection	400 A, 3 fuse type aR for internal 1000 A fuse type gG for upstream (normal duty) 800 A fuse type gG for upstream (heavy duty)
Energy efficiency ratio	0.98
Power dissipation in W	13330 W, total (normal duty) 9800 W, total (heavy duty) 1530 W, control part (normal duty) 1020 W, control part (heavy duty)
Volume of cooling air	1740 m <sup>3</sup> /h (power) 280 m <sup>3</sup> /h (control)
Noise level	71 dB conforming to 86/188/EEC - physical agents (noise) directive
Prospective line I <sub>sc</sub>	50 kA for 100 ms
Electrical connection	Control : removable screw terminals, 0.5...1.5 mm <sup>2</sup> Main supply : M12 bar Motor : M12 bar
Motor recommended cable cross section	5 x (3 x 120 mm <sup>2</sup> ) normal duty 4 x (3 x 185 mm <sup>2</sup> ) normal duty 3 x (3 x 185 mm <sup>2</sup> ) heavy duty 4 x (3 x 120 mm <sup>2</sup> ) heavy duty
Width	800 mm
Height	2150 mm
Depth	664 mm
Product weight	650 kg
Number of preset speeds	16 preset speeds
Communication port protocol	Modbus TCP Ethernet/IP Modbus serial
Option card	Slot A/slot B : digital and analog I/O extension module Slot A/slot B : output relay extension module Slot A : communication module, Profibus DP V1 Slot A : communication module, Profinet Slot A : communication module, DeviceNet Slot A : communication module, Modbus TCP/EtherNet/IP Slot A : communication module, CANopen daisy chain RJ45 Slot A : communication module, CANopen SUB-D 9 Slot A : communication module, CANopen screw terminals
Safety function	STO (safe torque off), level SIL 3 for <= 100 ms
EMC filter	Integrated conforming to EN/IEC 61800-3, category C3, shielded cable with <= 150 m maxi Integrated conforming to EN/IEC 61800-3, category C4, unshielded cable with <= 250 m maxi

## Complementary

Motor slip compensation	Can be suppressed Adjustable Automatic whatever the load Not available in permanent magnet motor law
Acceleration and deceleration ramps	S, U or customized Linear adjustable separately from 0.01 to 9000 s
Braking to standstill	By DC injection
Protection type	Motor : thermal protection Motor : safe torque off Motor : motor phase break Drive : thermal protection Drive : safe torque off Drive : overheating Drive : short-circuit protection Drive : motor phase break

	<p>Drive : line supply overvoltage          Drive : line supply undervoltage          Drive : line supply phase loss          Drive : overspeed          Drive : break on the control circuit          Drive : overcurrent (between output phases and earth)          Drive : overload (output)          Drive : overvoltage (DC bus)          Drive : short-circuit protection with semi-conductor fuse (main supply)          Drive : fan monitoring</p>
Frequency resolution	<p>Display unit : 0.1 Hz          Analog input : 0.012/50 Hz</p>
Connector type	<p>RJ45 (on the control block) for Modbus serial          RJ45 (on the control block) for Ethernet IP/Modbus TCP</p>
Physical interface	2-wire RS 485 for Modbus serial
Transmission frame	RTU for Modbus serial
Transmission rate	<p>10/100 Mbit/s for Ethernet IP/Modbus TCP          4.8, 9.6, 19.2, 38.4 kbit/s for Modbus serial</p>
Exchange mode	Half duplex, full duplex, autonegotiation for Ethernet IP/Modbus TCP
Data format	8 bits, configurable odd, even or no parity for Modbus serial
Type of polarization	No impedance for Modbus serial
Number of addresses	1...247 for Modbus serial
Method of access	Slave for Modbus TCP
Supply	<p>Internal supply for reference potentiometer (1 to 10 kOhm) : 10.5 V DC +/- 5 % current &lt;= 10 mA (overload and short-circuit protection)          Internal supply for digital inputs and STO : 24 V DC (21...27 V) current &lt;= 200 mA (overload and short-circuit protection)          External supply for digital inputs : 24 V DC (10...30 V) current &lt;= 1.25 mA (overload and short-circuit protection)</p>
Local signalling	LCD display unit operation function, status and configuration on front door
Analogue input number	3
Analogue input type	<p>Software-configurable voltage AI1, AI2, AI3 : 0...10 V DC impedance 30 kOhm , resolution 12 bits          Software-configurable current AI1, AI2, AI3 : 0...20 mA impedance 250 Ohm , resolution 12 bits</p>
Discrete input number	8
Discrete input type	<p>Programmable DI1...DI6 : 24 V DC (limits : &lt;= 30 V) impedance 3.5 kOhm          Programmable as pulse input DI5, DI6 0...30 kHz : 24 V DC (limits : &lt;= 30 V)          Safe torque off STOA, STOB : 24 V DC (limits : &lt;= 30 V) impedance &gt; 2.2 kOhm</p>
Input compatibility	<p>Discrete input DI1...DI6 : level 1 PLC conforming to EN/IEC 61131-2          Discrete input DI5, DI6 : level 1 PLC conforming to IEC 65A-68          Discrete input STOA, STOB : level 1 PLC conforming to EN/IEC 61131-2</p>
Discrete input logic	<p>DI1...DI6, positive logic (source) : &lt; 5 V (state 0) &gt; 11 V (state 1)          DI1...DI6, negative logic (sink) : &gt; 16 V (state 0) &lt; 10 V (state 1)          DI5, DI6, positive logic (source) : &lt; 0.6 V (state 0) &gt; 2.5 V (state 1)          STOA, STOB, positive logic (source) : &lt; 5 V (state 0) &gt; 11 V (state 1)</p>
Analogue output number	2
Analogue output type	<p>Software-configurable voltage AQ1, AQ2 : 0...10 V DC impedance 470 Ohm , resolution 10 bits          Software-configurable current AQ1, AQ2 : 0...20 mA , resolution 10 bits</p>
Sampling duration	<p>Discrete input DI1...DI4 : 2 ms (+/- 0.5 ms)          Discrete input DI5, DI6 : 5 ms (+/- 1 ms)          Analog input AI1, AI2, AI3 : 5 ms (+/- 1 ms)          Analog output AQ1, AQ2 : 10 ms (+/- 1 ms)</p>
Accuracy	<p>Analog input AI1, AI2, AI3 : +/- 0.6 % for a temperature variation 60 °C          Analog output AQ1, AQ2 : +/- 1 % for a temperature variation 60 °C</p>
Linearity error	<p>Analog input AI1, AI2, AI3 : +/- 0.15 % of maximum value          Analog output AQ1, AQ2 : +/- 0.2 %</p>
Relay output number	3
Relay output type	<p>Configurable relay logic R1 : fault relay NO/NC electrical durability 100000 cycles          Configurable relay logic R2 : sequence relay NO electrical durability 100000 cycles          Configurable relay logic R3 : sequence relay NO electrical durability 100000 cycles</p>
Refresh time	Relay output R1, R2, R3 : 5 ms (+/- 0.5 ms)
Minimum switching current	Relay output R1, R2, R3 : 5 mA at 24 V DC
Maximum switching current	<p>Relay output R1, R2, R3 on resistive load (cos phi = 1) : 3 A at 250 V AC          Relay output R1, R2, R3 on resistive load (cos phi = 1) : 3 A at 30 V DC          Relay output R1, R2, R3 on inductive load (cos phi = 0.4 L/R = 7 ms) : 2 A at 250 V AC</p>

Isolation	Between power and control terminals
<b>Environment</b>	
Insulation resistance	> 1 mOhm at 500 V DC for 1 minute to earth
Operating position	Vertical +/- 10 degree
Electromagnetic compatibility	1.2/50 $\mu$ s - 8/20 $\mu$ s surge immunity test level 3 conforming to IEC 61000-4-5 Electrical fast transient/burst immunity test level 4 conforming to IEC 61000-4-4 Electrostatic discharge immunity test level 3 conforming to IEC 61000-4-2 Radiated radio-frequency electromagnetic field immunity test level 3 conforming to IEC 61000-4-3 Conducted radio-frequency immunity test level 3 conforming to IEC 61000-4-6
Pollution degree	2 conforming to EN/IEC 61800-5-1
Vibration resistance	1.5 mm peak to peak (f= 3...10 Hz) conforming to IEC 60068-2-6 0.6 gn (f= 10...200 Hz) conforming to IEC 60068-2-6 3M3 conforming to IEC 60721-3-3
Shock resistance	4 gn (duration = 11 ms) conforming to IEC 60068-2-27 3M2 conforming to IEC 60721-3-3
Relative humidity	5...95 % without condensation conforming to IEC 60068-2-3
Ambient air temperature for operation	40...50 °C with derating factor -10...0 °C without derating with option enclosure heating 0...40 °C without derating
Ambient air temperature for storage	-25...70 °C
Operating altitude	< 1000 m without derating 2000...3800 m with current derating 1 % per 100 m for TT earthing system 2000...3800 m with current derating 1 % per 100 m for TN earthing system 2000...3800 m with current derating 1 % per 100 m for IT earthing system 3800...4800 m with current derating 1 % per 100 m for TT earthing system 3800...4800 m with current derating 1 % per 100 m for TN earthing system 1000...2000 m with current derating 1 % per 100 m
Environmental characteristic	Chemical pollution resistance class 3C3 conforming to EN/IEC 60721-3-3 Dust pollution resistance class 3S3 conforming to EN/IEC 60721-3-3 Humidity resistant class 3K3 conforming to EN/IEC 60721-3-3
Standards	EN/IEC 60204-1 EN/IEC 61800-5-1 EN/IEC 61800-3 EN/IEC 61800-2
Product certifications	EAC ATEX C-Tick
Marking	CE