

# Product data sheet

Specifications



Circuit breaker, PowerPacT B, 40A,  
2 pole, 600Y/347VAC, 18kA,  
terminal nut, thermal magnetic, 80%

BGF26040

## Main

Range	PowerPact
Product Name	PowerPact B
Device Short Name	BG 040
Product Or Component Type	Circuit breaker
Device Application	Distribution

## Complementary

[In] Rated Current	40 A
Number Of Poles	2P
Protected Poles Description	2t
Control Type	Toggle
Breaking Capacity Code	G
Breaking Capacity	65 kA at 208Y/120 V AC 50/60 Hz conforming to UL 489 65 kA at 240 V AC 50/60 Hz conforming to UL 489 35 kA at 480/277 V AC 50/60 Hz conforming to UL 489 35 kA at 480 V AC 50/60 Hz conforming to UL 489 20 kA at 250 V DC conforming to UL 489 18 kA at 600Y/347 V AC 50/60 Hz conforming to UL 489
[Ue] Rated Operational Voltage	525 V AC 50/60 Hz conforming to UL 489
Network Frequency	50/60 Hz
[Ics] Rated Service Breaking Capacity	65 kA at 220...240 V AC 50/60 Hz conforming to IEC 60947-2 18 kA at 500...525 V AC 50/60 Hz conforming to IEC 60947-2 35 kA at 380...415 V AC 50/60 Hz conforming to IEC 60947-2 35 kA at 440 V AC 50/60 Hz conforming to IEC 60947-2
[Uimp] Rated Impulse Withstand Voltage	8 kV conforming to IEC 60947-2
Trip Unit Technology	Thermal-magneticTM-D,
Continuous Current Rating	80 %
[Ui] Rated Insulation Voltage	800 V conforming to IEC 60947-2
Trip Unit Name	TM-D
Suitability For Isolation	Yes conforming to IEC 60947-2
Utilisation Category	Category A
Mechanical Durability	15000 cycles conforming to IEC 947-1 Annex K ed 5.2
Electrical Durability	10000 cycles conforming to IEC 947-1 Annex K ed 5.2 at 440 V In
Connection Pitch	27 mm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Awg Gauge	AWG 14...AWG 8 aluminium/copper AWG 6...AWG 3/0 aluminium/copper
Local Signalling	Presence of auxiliary contacts: flag (green)
Mounting Mode	Clip-on (35 mm symmetrical DIN rail) By screws (plate)
Electrical Connection	Terminal nut, ON and OFF end
Tightening Torque	5 N.m for 2.5...16 mm² (AWG 14...AWG 4) 9 N.m for 25...95 mm² (AWG 3...AWG 3/0)
Number Of Slots	1 slot(s) for auxiliary switch OF (plug-in) 1 slot(s) for voltage release MN or MX (plug-in)
Power Wire Stripping Length	20 mm
Color	Grey (RAL 7016)
9 Mm Pitches	6
Height	137 mm
Width	54 mm
Depth	80 mm
Net Weight	0.669 kg
Quantity Per Set	Set of 1
Circuit Breaker Application	HACR rated

## Environment

Quality Labels	CE
Standards	GB 14048.2 NEMA AB1 NMX J-266 UL 489 EN/IEC 60947-2 CSA C22.2 No 5 EN/IEC 60947-5-1
Product Certifications	UL IEC CCC EAC CSA NOM
Ip Degree Of Protection	Front cover: IP40 conforming to IEC 60529
Ik Degree Of Protection	IK07 conforming to IEC 62262
Pollution Degree	3 conforming to IEC 60947-1
Ambient Air Temperature For Operation	-25...70 °C
Ambient Air Temperature For Storage	-50...85 °C
Operating Altitude	2000 m without derating 5000 m with derating

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	6.096 cm
Package 1 Width	11.938 cm
Package 1 Length	20.574 cm

---

Package 1 Weight	680.389 g
------------------	-----------

# Sustainability

**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information   [Yes](#)

✓ Pvc Free

✓ Halogen Free Product

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: DINP, which is known to the State of California to cause cancer, and DIDP, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="#">www.P65Warnings.ca.gov</a>