# Product data sheet

Specifications



# Control relay, TeSys Deca, 3NO+2NC, 0 to 690V, 220VAC 50/60Hz standard coil, screw clamp

CAD32M7

### Main

Range	TeSys TeSys Deca	
Product Name	TeSys CAD	
Product Or Component Type	Control relay	
Device Short Name	CAD	
Contactor Application	Control circuit	

### Complementary

Complementary		
Utilisation Category	DC-13 AC-14 AC-15	
Pole Contact Composition	3 NO + 2 NC	
[Ue] Rated Operational Voltage	<= 690 V AC 25400 Hz	
Control Circuit Type	AC at 50/60 Hz	
[Uc] Control Circuit Voltage	220 V AC 50/60 Hz	
[Uimp] Rated Impulse Withstand Voltage	6 kV conforming to IEC 60947	
[Ith] Conventional Free Air Thermal Current	10 A (at 60 °C)	
Irms Rated Making Capacity	140 A AC conforming to IEC 60947-5-1 250 A DC conforming to IEC 60947-5-1	
[Icw] Rated Short-Time Withstand Current	100 A - 1 s 120 A - 500 ms 140 A - 100 ms	
Associated Fuse Rating	10 A gG conforming to IEC 60947-5-1	
[Ui] Rated Insulation Voltage	600 V UL certified 600 V CSA certified 690 V conforming to IEC 60947-5-1	
Mounting Support	Plate Rail	
Connections - Terminals	nals       Screw clamp terminals 1 cable(s) 14 mm²flexible without cable end         Screw clamp terminals 2 cable(s) 14 mm²flexible without cable end         Screw clamp terminals 1 cable(s) 14 mm²flexible with cable end         Screw clamp terminals 2 cable(s) 14 mm²flexible with cable end         Screw clamp terminals 2 cable(s) 14 mm²flexible with cable end         Screw clamp terminals 1 cable(s) 14 mm²flexible with cable end         Screw clamp terminals 1 cable(s) 14 mm²flexible with cable end         Screw clamp terminals 2 cable(s) 14 mm²solid without cable end         Screw clamp terminals 2 cable(s) 14 mm²solid without cable end         Screw clamp terminals 2 cable(s) 14 mm²solid without cable end	
Tightening Torque	<ul> <li>1.2 N.m - on screw clamp terminals - with screwdriver Philips No 2</li> <li>1.2 N.m - on screw clamp terminals - with screwdriver flat Ø 6 mm</li> <li>1.2 N.m - on screw clamp terminals - with screwdriver pozidriv No 2</li> </ul>	

Control Circuit Voltage Limits	0.30.6 Uc (-4070 °C):drop-out AC 50/60 Hz 0.81.1 Uc (-4060 °C):operational AC 50 Hz 0.851.1 Uc (-4060 °C):operational AC 60 Hz 11.1 Uc (6070 °C):operational AC 50/60 Hz	
Operating Time	<ul> <li>1222 ms coil energisation and NO closing</li> <li>412 ms coil de-energisation and NO opening</li> <li>419 ms coil energisation and NC opening</li> <li>617 ms coil de-energisation and NC closing</li> </ul>	
Mechanical Durability	30 Mcycles	
Maximum Operating Rate	180 cyc/mn	
Inrush Power In Va	70 VA 50 Hz (at 20 °C)	
Hold-In Power Consumption In Va	8 VA 50 Hz (at 20 °C)	
Minimum Switching Voltage	17 V	
Minimum Switching Current	5 mA	
Non-Overlap Time	1.5 ms on energisation between NC and NO contact 1.5 ms on de-energisation between NC and NO contact	
Insulation Resistance	> 10 MOhm	
Mechanical Robustness	Shocks control relay open: 10 Gn for 11 ms conforming to IEC 60068-2-27 Shocks control relay closed: 15 Gn for 11 ms conforming to IEC 60068-2-27 Vibrations control relay open: 2 Gn, 5300 Hz conforming to IEC 60068-2-6 Vibrations control relay closed: 4 Gn, 5300 Hz conforming to IEC 60068-2-6	
Height	77 mm	
Width	45 mm	
Depth	84 mm	
Net Weight	0.58 kg	

## Environment

Standards	EN/IEC 60947-5-1 GB/T 14048.5 UL 60947-5-1 CSA C22.2 No 60947-5-1 JIS C8201-5-1	
Product Certifications	CB CCC UL CSA EAC CE UKCA	
Ip Degree Of Protection	IP2X front face conforming to VDE 0106	
Protective Treatment	TH conforming to IEC 60068	
Ambient Air Temperature For Operation	-4060 °C 6070 °C with derating	
Ambient Air Temperature For Storage	-6080 °C	
Operating Altitude	03000 m	

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.000 cm
Package 1 Width	9.000 cm

Package 1 Length	11.000 cm
Package 1 Weight	348.000 g
Unit Type Of Package 2	S02
Number Of Units In Package 2	20
Package 2 Height	15.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	7.197 kg
Unit Type Of Package 3	P06
Number Of Units In Package 3	320
Package 3 Height	75.000 cm
Package 3 Width	80.000 cm
Package 3 Length	60.000 cm
Package 3 Weight	123.152 kg

### **Contractual warranty**

Warranty

18 months

### Sustainability

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Yes

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

#### Well-being performance



Eq

Rohs Exemption Information

### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information
California Proposition 65	WARNING: This product can expose you to chemicals including: Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov