

# Product data sheet

Specifications



## EasyCan Capacitor - 14.4/17.3 kvar - 480 V - 50/60Hz

BLRCS144A173B48

⚠ Discontinued on: May 2, 2023

⚠ Discontinued

### Main

Range Of Product	EasyCan
Product Or Component Type	Standard duty capacitor
Network Frequency	50/60 Hz
Series Name	EasyCan
Network Harmonic Content	<= 10 %
Electrical Parameters	14.4 kvar 480 V 50 Hz 17.3 kvar 480 V 60 Hz
Maximum Permissible Voltage	1.1 x Un (8 hours over 24 hours)
Continuous Overcurrent Capacity	1.5 x In
Rated Voltage	480 V AC 50/60 Hz

### Complementary

Dielectric Losses	< 0.2 W/kvar
Power Losses	< 0.5 W/kVAr
Capacitance Tolerance	- 5 % to 10 %
Voltage Test	2.15 x Un AC between terminals for 10 s <= 660 V - 3 kV AC between terminal and container for 10 s >= 660 V - 6 kV AC between terminal and container for 10 s
Inrush Current	200 x In
Maximum Switching Operation Per Year	5000
Service Life In Hours	100000 h
Dielectric Material	Metallized polypropylene film with Zn/Al alloy,
Impregnation Material	Non-PCB soft PUR resin Biodegradable
Type Of Installation	Indoor installation
Connections - Terminals	ClampTite terminal
Mounting Mode	Vertical
Diameter	75 mm
Height	308 mm
Net Weight	1.3 kg

### Environment

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Standards	IEC 60831-2
	IEC 60831-1
Ip Degree Of Protection	IP20
Operating Altitude	2000 m
Temperature Class	D
Ambient Air Temperature For Operation	-25...55 °C
Relative Humidity	95 %

## Contractual warranty

Warranty	18 months
----------	-----------