

Product data sheet

Specifications



Acti9 - IC2000 - twilight switch - 2... 2000 lux

CCT15284

❗ Discontinued on: May 31, 2019

❗ End-of-service on: Oct 2, 2020

❗ Discontinued

Main

Range Of Product	Acti9
Product Name	Acti9 IC
Product Or Component Type	Twilight switch
Device Short Name	IC2000
Provided Equipment	switchboard cell
Load Type	230 V AC halogen lamp: 2300 W 230 V AC incandescent lamp: 2300 W dual mounted fluorescent tube with conventional ballast: 2300 VA dual mounted fluorescent tube with electronic ballast: 300 VA fluocompact lamp with conventional ballast: 1500 VA non-corrected fluorescent tube with conventional ballast: 2300 VA parallel-corrected fluorescent tube with conventional ballast: 400 VA parallel-corrected mercury and sodium vapour lamps: 400 VA serial-corrected fluorescent tube with conventional ballast: 2300 VA 7 x 11 W fluocompact lamp with electronic ballast 7 x 15 W fluocompact lamp with electronic ballast 7 x 20 W fluocompact lamp with electronic ballast 7 x 23 W fluocompact lamp with electronic ballast 9 x 7 W fluocompact lamp with electronic ballast
Function Available	Cabling test function with a push-button on front face

Complementary

Device Application	Building
Number Of Channels	1
Power Consumption In Va	6 VA
[Ue] Rated Operational Voltage	230 V AC +10 % -15 % at 50/60 Hz
Maximum Switching Current	10 A - 250 V AC pf = 0.6 16 A - 250 V AC pf = 1
Electrical Insulation Class	Class II
Opening Distance	< 3 mm
Status Led	LED (green) threshold reached LED (red) brightness less than the threshold
Time Delay	>= 60 s on closing >= 60 s on breaking contact
9 Mm Pitches	5
Light Intensity Adjustment	2...2000 lux
Connections - Terminals	2 x 2.5 mm² screwless terminals
Height	85 mm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Width	45 mm
Depth	65 mm
Net Weight	280 g
Control Type	By brightness detection
Market Segment	Small commercial Residential
Compatibility Code	IC2000

Environment

Ambient Air Temperature For Operation	-25...50 °C
Ip Degree Of Protection	IP20 B
Standards	EN 60669 EN 60529

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	9 cm
Package 1 Width	9 cm
Package 1 Length	11 cm
Package 1 Weight	308 g

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Certifications & Standards

Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information