

# Product data sheet

Specifications



## Acti9 IC2000 outdoor (2 - 2000 lux) twilight switch

CCT15369

### Main

Range Of Product	Acti9
Product Name	Acti9 IC
Product Or Component Type	Twilight switch
Device Short Name	IC2000
Provided Equipment	twilight sensor outdoor
Load Type	incandescent lamp: 2600 W halogen lamp: 2600 W non-corrected fluorescent tube: 2300 VA serial-compensated fluorescent tube: 2300 VA parallel compensated fluorescent lamp: 730 VA (80 µF) compact fluorescent lamp: 170 W < 2 W LED lamp: 30 W > 2 W LED lamp: 200 W

### Complementary

Device Application	Building
Number Of Channels	1
Maximum Power Consumption In W	0.5 W stand by
[Ue] Rated Operational Voltage	230 V AC +10 % -15 % at 50/60 Hz
Maximum Switching Current	10 A - 250 V AC pf = 0.6 16 A - 250 V AC pf = 1
Minimum Switching Current	10 mA 230 V AC 100 mA 24 V AC/DC
Electrical Insulation Class	Class II
Output Type	Dry contact
Accuracy	+/- 0.25 s/day 25 °C
Contacts Type And Composition	1 NO
Time Delay	20 s on 80 s off
Light Intensity Adjustment	2...2000 lux
Connections - Terminals	1 x 2.5 mm² screw terminals solid or flexible with sleeve 2 x 0.5...2.5 mm² screw terminals solid or flexible
Mounting Support	TH35 DIN rail conforming to EN 60715
Height	85.5 mm
Width	18 mm
Depth	67 mm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Net Weight	111 g
Overvoltage Category	Class 3
Marking	CE
Control Type	By brightness detection

## Environment

Ambient Air Temperature For Operation	-30...55 °C
Ambient Air Temp For Storage/ Transportation	-30...70 °C
Relative Humidity	90 %, non-condensing
Ip Degree Of Protection	IP20 IP55 (sensor)
Standards	EN 60669-2-1

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	6.5 cm
Package 1 Width	8.0 cm
Package 1 Length	10.5 cm
Package 1 Weight	161.0 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	40
Package 2 Height	30 cm
Package 2 Width	30 cm
Package 2 Length	40 cm
Package 2 Weight	6.89 kg
Package 3 Height	80 cm

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance



Mercury Free



RoHS Exemption Information

Yes

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	<a href="#">End of Life Information</a>