

# Product data sheet

Specifications



## Acti9 - IHP+ - 1C digital time switch - 24 hours + 7 days

CCT15401

⚠ Discontinued on: May 31, 2019

⚠ End-of-service on: Oct 2, 2020

⚠ Discontinued

### Main

Range Of Product	Acti9
Product Name	Acti9 IHP
Device Short Name	IHP
Product Or Component Type	Programmable digital time switch
Device Application	Building
Battery Type	Lithium
Number Of Channels	1
Available Equipment	Memory key
Language	Russian English Lituanien Estonian Latvian Ukrainian
Colour Tint	White (RAL 9003)

### Complementary

Product Compatibility	Mechanical compatibility with electrical distribution comb busbars
Power Consumption In Va	4 VA
Maximum Switching Current	10 A - 250 V AC pf = 0.6 16 A - 250 V AC pf = 1
[Ue] Rated Operational Voltage	230 V AC +/- 10 % at 50/60 Hz
Number Of Inputs	1 input(s) impulse and maintained
Accuracy	+/- 1 s/day 20 °C
Cycle Duration	24 hours + 7 days
Maximum Number Of Switchings	84
Minimum Interval Duration	1 s
Function Available	Pulse programming Automatic winter/summer time changeover
Display Type	Backlit LCD
Battery Life	6 year(s)
Backup Time	6 years time and program saving
Type Of Setting	Absence for holidays function Random function

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Connections - Terminals	screwless terminals
Mounting Support	DIN rail
9 Mm Pitches	5
Width	45 mm
Height	85 mm
Depth	66 mm
Function	Pulse programming and random function
Absence For Holidays	Yes
Time Changeover	Automatic
Updated By	None
Compatibility Code	IHP
Market Segment	Small commercial

## Environment

Ambient Air Temperature For Operation	-10...50 °C
Ip Degree Of Protection	IP20 B

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8 cm
Package 1 Width	5 cm
Package 1 Length	10.7 cm
Package 1 Weight	0.19 kg

## Contractual warranty

Warranty	18 months
----------	-----------

# Sustainability

**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency   RoHS/REACH

## Certifications & Standards

Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End of Life Information</a>