

Product data sheet

Specifications



STD - DIN - remote control dimmer - 400 W

CCTDD20001

Main

Range Of Product	Acti9
Product Name	Acti9 STD
Product Or Component Type	Remote control dimmer
Device Short Name	STD
Product Compatibility	Power regulators designed
Function Available	Automatic load type detection

Complementary

Device Application	Building
Load Type	230 V AC halogen lamp: 40...400 W 230 V AC incandescent lamp: 40...400 W low voltage halogen lamp with electronic transformer: 40...400 W motor: 40...200 W low voltage halogen lamp with conventional transformer: 40...400 W low voltage halogen lamp with toroidal transformer: 40...300 W
Control Type	Local control: push-button Remote control: push-button
Power Consumption In Va	0.8 VA
Thermal Losses	3 W
[Ue] Rated Operational Voltage	230 V AC +/- 10 % at 50 Hz
Protection Type	Electronic overload protection Electronic over temperature protection Electronic overvoltage protection Single shot thermal fuse
Mounting Support	DIN rail
9 Mm Pitches	4
Connected Auxiliaries	Maximum 25 auxiliary push-buttons without light indication, distance : < 50 m Maximum 5 auxiliary push-buttons with light indication, distance : < 50 m
Connections - Terminals	Screw terminals, 2 cable(s) 4 mm² top
Height	85 mm
Width	36 mm
Depth	62 mm
Net Weight	80 g

Environment

Ip Degree Of Protection	IP20
-------------------------	------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Standards	EN 60669-2-1
Directives	73/23/EEC - low voltage directive 89/336/EEC - electromagnetic compatibility
Ambient Air Temperature For Operation	0...70 °C
Ambient Air Temperature For Storage	0...60 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8.0 cm
Package 1 Width	9.5 cm
Package 1 Length	9.5 cm
Package 1 Weight	137.0 g

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information