

Product data sheet

Specifications



Magnetic latching contactor, TeSys F, 3P(3NO), AC-3 ≤440V 265A, 240V AC coil

CR1F265U7

Main

Range	TeSys
Product Name	TeSys F
Product Or Component Type	Magnetic latching contactor
Device Short Name	CR1F
Device Application	Control
Contactor Application	Resistive load Motor control
Utilisation Category	AC-3 AC-4 AC-1
Poles Description	3P
Power Pole Contact Composition	3 NO
[Ue] Rated Operational Voltage	1000 V AC 25...200 Hz
[Ie] Rated Operational Current	265 A (at <40 °C) at ≤ 440 V AC AC-3 350 A (at <40 °C) at ≤ 440 V AC AC-1 245 A (at <40 °C) at ≤ 440 V AC AC-4
Motor Power Kw	132 kW at 400 V AC 50/60 Hz (AC-4)
Control Circuit Type	AC at 50/60 Hz
[Uc] Control Circuit Voltage	240 V AC 50/60 Hz
Irms Rated Making Capacity	2940 A
Rated Breaking Capacity	2450 A at 220...440 V 2200 A at 500 V 800 A at 1000 V 1700 A at 660/690 V
[Icw] Rated Short-Time Withstand Current	2200 A 40 °C - 1 s 2200 A 40 °C - 5 s 2200 A 40 °C - 10 s 1230 A 40 °C - 30 s 950 A 40 °C - 1 min 620 A 40 °C - 3 min 480 A 40 °C - 10 min
Associated Fuse Rating	315 A aM at ≤ 440 V 400 A BS88 at ≤ 440 V 400 A gG at ≤ 440 V
Average Impedance	0.32 mOhm - Ith 350 A 50 Hz
[Ui] Rated Insulation Voltage	1000 V conforming to IEC 60158-1 1000 V conforming to IEC 60947-4 1000 V conforming to BS 775 1500 V conforming to VDE 0110 group C
Power Dissipation Per Pole	22 W AC-3 39 W AC-1

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Standards	EN/IEC 60947-1 EN/IEC 60947-4-1 JIS C8201-4-1 UL 60947-4-1 CSA C22.2 No 60947-4-1
Product Certifications	CB Scheme UL CSA EAC CE UKCA
Connections - Terminals	Lugs-ring terminals 1 cable(s) 240 mm² Connector 1 cable(s) 240 mm² Bars 2 cable(s) - busbar cross section: 32 x 4 mm Power circuit: bolted connection
Tightening Torque	35 N.m
Operating Time	40...75 ms latching 50...100 ms unlatching
Mechanical Durability	1 Mcycles
Maximum Operating Rate	120 cyc/h 40 °C

Complementary

Control Circuit Voltage Limits	Latching: 0.85...1.1 Uc Unlatching: 0.85...1.1 Uc
Average Consumption	1650 VA AC 50/60 Hz latching 9 VA AC 50/60 Hz unlatching

Environment

Protective Treatment	TC
Ambient Air Temperature For Operation	-15...70 °C
Ambient Air Temperature For Storage	-60...80 °C
Operating Altitude	3000 m without derating
Height	203 mm
Width	201.5 mm
Depth	213 mm
Net Weight	7.4 kg

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	25.0 cm
Package 1 Width	25.0 cm
Package 1 Length	25.1 cm
Package 1 Weight	8.03 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

✓ Pvc Free

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov