

Product data sheet

Characteristics

CSU0860264916

Stago - KG281 tray side perforation 60x120mm
L=4.5m 1mm pre-galvanized RAL9016



Main

Range of product	Stago
Product or component type	Cable tray
Cable support type	Perforated
Mounting location	Partly outdoor environment with low exposure to corrosion ware-houses and parking garages

Complementary

Product destination	KG281 cable tray
Fixing mode	Screwless
Material with surface treatment	Steel pre-galvanized, RAL 9016
Corrosion class	C2
Thickness	1 mm
Perforation location	Side perforation
Nominal cross section	7200 mm ²
Height	60 mm
Width	120 mm
Length	4500 mm
Net weight	2.095 kg / 100 m

Offer Sustainability

REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Not applicable, out of EU RoHS legal scope
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Circularity Profile	No need of specific recycling operations

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications