

# Product data sheet

Specifications



## Stago - horizontal bend 90° formed 60x300mm stainless steel AISI 316

CSU76623040

 **Discontinued on:** Sep 19, 2018

 **Discontinued**

### Main

|                           |       |
|---------------------------|-------|
| Range Of Product          | Stago |
| Product Or Component Type | Bend  |

### Complementary

|                                 |                                     |
|---------------------------------|-------------------------------------|
| Operating Angle                 | 90 °                                |
| Direction Change Type           | Horizontal                          |
| Inner Radius                    | 100 mm                              |
| Adjustment                      | Fixed                               |
| Product Destination             | Cable tray ES114 H= 60 mm W= 300 mm |
| Fixing Mode                     | By screw                            |
| Material With Surface Treatment | Stainless steel AISI 316            |
| Corrosion Class                 | C5-M                                |
| Height                          | 63 mm                               |
| Width                           | 505 mm                              |
| Depth                           | 505 mm                              |

### Environment

|                   |                                                                                                               |
|-------------------|---------------------------------------------------------------------------------------------------------------|
| Mounting Location | Area with almost permanent high levels of humidity, airborne pollution and salt purifying plants and offshore |
|-------------------|---------------------------------------------------------------------------------------------------------------|

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications