

Product data sheet

Specifications



10AX 250V Surface Mount Two Gang Two Way Switch IP66

CSW110_2

Main

Range	Kavacha
Product Or Component Type	Switch
Device Short Name	AS

Complementary

Wiring Device Mounting	Surface
Switch Function	2-way switch with looping terminal
Rated Current	10 AX at 250 V AC
Number Of Gangs	2 gangs
Width	80 mm
Height	103 mm
Depth	65 mm

Environment

Environmental Characteristic	Weatherproof
Ip Degree Of Protection	IP66
Standards	IEC 60529 BS EN 60669-1 : 2000

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8 cm
Package 1 Width	10.3 cm
Package 1 Length	6.5 cm
Package 1 Weight	0.001 g

Contractual warranty

Warranty	18 months
----------	-----------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications