



## Main

Range	TeSys
Device short name	DF14
Product or component type	Auxiliary contact block
Auxiliary contacts operation	Instantaneous
Pole contact composition	1 NC
Connections - terminals	Faston connector

## Complementary

Range compatibility	TeSys DF
[Ui] rated insulation voltage	250 VAC
[Ue] rated operational voltage	24...240 V AC AC-15 24...240 V DC DC-13
[Ith] conventional free air thermal current	5 A
Minimum switching current	30 mA
Minimum switching voltage	10 V
Net weight	0.025 kg

## Environment

Ambient air temperature for operation	-20...60 °C
Ambient air temperature for storage	-40...80 °C

## Offer Sustainability

RECh Regulation	<a href="#">RECh Declaration</a>
RECh free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a>

---

WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
------	---

---

**Contractual warranty**

---

Warranty	18 months
----------	-----------

---