

Product data sheet

Specifications



AC servo motor BSH, Lexium 05,
0.9N.m, 4000rpm, untapped shaft,
with brake, IP65

BSH0552P22F1A

Main

Product Or Component Type	Servo motor
Device Short Name	BSH
Maximum Mechanical Speed	9000 rpm
Continuous Stall Torque	0.8 N.m for LXM32.U60N4 at 1.5 A, 400 V, three phase 0.8 N.m for LXM32.U60N4 at 1.5 A, 480 V, three phase 0.9 N.m for LXM05CU70M2, 200...240 V, single phase 0.9 N.m for LXM05AD10M2, 200...240 V, single phase 0.9 N.m for LXM05BD10M2, 200...240 V, single phase 0.9 N.m for LXM05CD10M2, 200...240 V, single phase 0.9 N.m for LXM05AD10M3X, 200...240 V, three phase 0.9 N.m for LXM05BD10M3X, 200...240 V, three phase 0.9 N.m for LXM05CD10M3X, 200...240 V, three phase 0.9 N.m for LXM15LD13M3, 230 V, single phase 0.9 N.m for LXM15LD13M3, 230 V, three phase 0.9 N.m for LXM15LU60N4, 230 V, three phase 0.9 N.m for LXM05AD14N4, 380...480 V, three phase 0.9 N.m for LXM05BD14N4, 380...480 V, three phase 0.9 N.m for LXM05CD14N4, 380...480 V, three phase
Peak Stall Torque	2.5 N.m for LXM32.U60N4 at 1.5 A, 400 V, three phase 2.5 N.m for LXM32.U60N4 at 1.5 A, 480 V, three phase 2.5 N.m for LXM15LD13M3, 230 V, single phase 2.17 N.m for LXM05CU70M2, 200...240 V, single phase 2.7 N.m for LXM05AD10M2, 200...240 V, single phase 2.7 N.m for LXM05BD10M2, 200...240 V, single phase 2.7 N.m for LXM05CD10M2, 200...240 V, single phase 2.5 N.m for LXM15LD13M3, 230 V, three phase 2.26 N.m for LXM15LU60N4, 230 V, three phase 2.7 N.m for LXM05AD10M3X, 200...240 V, three phase 2.7 N.m for LXM05AD14N4, 380...480 V, three phase 2.7 N.m for LXM05BD10M3X, 200...240 V, three phase 2.7 N.m for LXM05BD14N4, 380...480 V, three phase 2.7 N.m for LXM05CD10M3X, 200...240 V, three phase 2.7 N.m for LXM05CD14N4, 380...480 V, three phase
Nominal Output Power	400 W for LXM32.U60N4 at 1.5 A, 400 V, three phase 400 W for LXM32.U60N4 at 1.5 A, 480 V, three phase 250 W for LXM05AD10M2, 200...240 V, single phase 250 W for LXM05BD10M2, 200...240 V, single phase 250 W for LXM05CD10M2, 200...240 V, single phase 250 W for LXM05CU70M2, 200...240 V, single phase 310 W for LXM15LD13M3, 230 V, single phase 250 W for LXM05AD10M3X, 200...240 V, three phase 250 W for LXM05AD14N4, 380...480 V, three phase 250 W for LXM05BD10M3X, 200...240 V, three phase 250 W for LXM05BD14N4, 380...480 V, three phase 250 W for LXM05CD10M3X, 200...240 V, three phase 250 W for LXM05CD14N4, 380...480 V, three phase 310 W for LXM15LD13M3, 230 V, three phase 310 W for LXM15LU60N4, 230 V, three phase

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Nominal Torque	0.65 N.m for LXM32.U60N4 at 1.5 A, 400 V, three phase 0.65 N.m for LXM32.U60N4 at 1.5 A, 480 V, three phase 0.75 N.m for LXM15LD13M3, 230 V, single phase 2.17 N.m for LXM05CU70M2, 200...240 V, single phase 2.7 N.m for LXM05AD10M2, 200...240 V, single phase 2.7 N.m for LXM05BD10M2, 200...240 V, single phase 2.7 N.m for LXM05CD10M2, 200...240 V, single phase 0.75 N.m for LXM15LD13M3, 230 V, three phase 0.75 N.m for LXM15LU60N4, 230 V, three phase 2.7 N.m for LXM05AD10M3X, 200...240 V, three phase 2.7 N.m for LXM05AD14N4, 380...480 V, three phase 2.7 N.m for LXM05BD10M3X, 200...240 V, three phase 2.7 N.m for LXM05BD14N4, 380...480 V, three phase 2.7 N.m for LXM05CD10M3X, 200...240 V, three phase 2.7 N.m for LXM05CD14N4, 380...480 V, three phase
Nominal Speed	6000 rpm for LXM32.U60N4 at 1.5 A, 400 V, three phase 6000 rpm for LXM32.U60N4 at 1.5 A, 480 V, three phase 4000 rpm for LXM15LD13M3, 230 V, single phase 4000 rpm for LXM15LU60N4, 230 V, three phase 3000 rpm for LXM05CU70M2, 200...240 V, single phase 3000 rpm for LXM05AD10M2, 200...240 V, single phase 3000 rpm for LXM05BD10M2, 200...240 V, single phase 3000 rpm for LXM05CD10M2, 200...240 V, single phase 3000 rpm for LXM05AD10M3X, 200...240 V, three phase 3000 rpm for LXM05AD14N4, 380...480 V, three phase 3000 rpm for LXM05BD10M3X, 200...240 V, three phase 3000 rpm for LXM05BD14N4, 380...480 V, three phase 3000 rpm for LXM05CD10M3X, 200...240 V, three phase 3000 rpm for LXM05CD14N4, 380...480 V, three phase 4000 rpm for LXM15LD13M3, 230 V, three phase
Product Compatibility	LXM05AD10M2 at 200...240 V single phase LXM05BD10M2 at 200...240 V single phase LXM05CD10M2 at 200...240 V single phase LXM05CU70M2 at 200...240 V single phase LXM15LD13M3 at 230 V single phase LXM15LU60N4 at 230 V three phase LXM32.U60N4 at 400 V three phase LXM32.U60N4 at 480 V three phase LXM05AD10M3X at 200...240 V three phase LXM05BD10M3X at 200...240 V three phase LXM05CD10M3X at 200...240 V three phase LXM15LD13M3 at 230 V three phase LXM05AD14N4 at 380...480 V three phase LXM05BD14N4 at 380...480 V three phase LXM05CD14N4 at 380...480 V three phase
Shaft End	Untapped
Ip Degree Of Protection	IP65 standard IP67 with IP67 kit
Speed Feedback Resolution	131072 points/turn x 4096 turns
Holding Brake	With
Mounting Support	International standard flange
Electrical Connection	Straight connectors

Complementary

Range Compatibility	Lexium 15 Lexium 32 Lexium 05
Supply Voltage Max	480 V
Network Number Of Phases	Three phase
Continuous Stall Current	1.2 A
Maximum Continuous Power	0.67 W

Maximum Current Irms	5.9 A for LXM15LD13M3 5.9 A for LXM15LU60N4 4.8 A for LXM05CU70M2 4.8 A for LXM05AD10M2 4.8 A for LXM05AD10M3X 4.8 A for LXM05AD14N4 4.8 A for LXM05BD10M2 4.8 A for LXM05BD10M3X 4.8 A for LXM05BD14N4 4.8 A for LXM05CD10M2 4.8 A for LXM05CD10M3X 4.8 A for LXM05CD14N4 4.8 A for LXM32.U60N4
Maximum Permanent Current	4.8 A
Switching Frequency	8 kHz
Second Shaft	Without second shaft end
Shaft Diameter	9 mm
Shaft Length	20 mm
Feedback Type	Multiturn SinCos Hiperface
Holding Torque	0.8 N.m holding brake
Motor Flange Size	55 mm
Number Of Motor Stacks	2
Torque Constant	0.7 N.m/A at 120 °C
Back Emf Constant	40 V/krpm at 120 °C
Number Of Motor Poles	6
Rotor Inertia	0.1173 kg.cm²
Stator Resistance	17.4 Ohm at 20 °C
Stator Inductance	35.3 mH at 20 °C
Stator Electrical Time Constant	2.03 ms at 20 °C
Maximum Radial Force Fr	190 N at 7000 rpm 190 N at 8000 rpm 200 N at 6000 rpm 220 N at 5000 rpm 230 N at 4000 rpm 260 N at 3000 rpm 290 N at 2000 rpm 370 N at 1000 rpm
Maximum Axial Force Fa	0.2 x Fr
Brake Pull-In Power	10 W
Type Of Cooling	Natural convection
Length	181 mm
Centring Collar Diameter	40 mm
Centring Collar Depth	2 mm
Number Of Mounting Holes	4
Mounting Holes Diameter	5.5 mm
Circle Diameter Of The Mounting Holes	63 mm
Net Weight	1.6 kg

Packing Units

Unit Type Of Package 1	PCE
------------------------	-----

Number Of Units In Package 1	1
Package 1 Height	12.3 cm
Package 1 Width	12.8 cm
Package 1 Length	37.7 cm
Package 1 Weight	1.25 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

✓ Pvc Free


Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Dimensions Drawings

Servo Motors Dimensions

Example with Straight Connectors



- a: Power supply for servo motor brake
b: Power supply for servo motor encoder
(1) M4 screw
(2) Shaft end, keyed slot (optional)
(3) For screw M3 x 9 mm/M3 x 0.35 in.

Dimensions in mm

Straight connectors		Rotatable angled connectors		c (without brake)	c (with brake)
b	b1	b	b1		
39.5	25.5	39.5	39.5	154.5	181

Dimensions in in.


Straight connectors		Rotatable angled connectors		c (without brake)	c (with brake)
b	b1	b	b1		
1.55	1.00	1.55	1.55	6.08	7.12

Performance Curves

400 V 3-Phase Supply Voltage

Torque/Speed Curves

Servo motor with LXM32•U60N4 servo drive




- X Speed in rpm
- Y Torque in Nm
- 1 Peak torque
- 2 Continuous torque

480 V 3-Phase Supply Voltage

Torque/Speed Curves

Servo motor with LXM32•U60N4 servo drive



- X Speed in rpm
- Y Torque in Nm
- 1 Peak torque
- 2 Continuous torque